



America's Favorite Transfer Switches
For Backup Power Applications



CALL NOW: 1.888.GEN.TRAN

SEARCH ITEMS

GO

[Advanced Search](#)

OUR PRODUCTS

Manual Transfer Switches

- PowerStay Manual Transfer Switches for 6-16 circuits
- Prewired Manual Transfer Switches for 6-10 circuits
- Compact Manual Transfer Switches for 1-2 circuits
- Power Centers – Service Entrance Rated Transfer Switches
- Vintage Prewired Transfer Switches
- Options and Accessories

GenShed Generator Shelter

Generator-Ready Load Centers

Transfer Switches For Traffic Signals

Automatic Transfer Switches

Power Inlet Boxes

Power Cords

Plugs and Connectors

PowerWeb™ Temporary Power Distribution Centers

Parallel Power Kits

Generator Accessories

Installation Tools

Service Parts

SPECIAL OFFERS

CLEARANCE ITEMS

We Accept:



GenTran Corporation is certified as a Women's Business Enterprise through the Women's Business Enterprise National Council (WBENC).



<http://www.WBENC.org>

Prewired 6-circuit 30 amp manual transfer switch, no meters, no inlet



This UL LISTED prewired generator transfer switch is our most economical ever! It's ideal for basement installations when you want to power just the essential appliances with a portable generator during a power outage. It accommodates 6 to 10 household circuits, and can be used with any portable generator up to 7500 watts (continuous). Ideal for powering your furnace blower (gas only), refrigerator and kitchen circuits, well pump, lights, and television. If your needs change, you can easily expand this transfer switch to up to 10 circuits just by adding more circuit breakers. The enclosure can be surface mounted indoors, and accommodates hardwired generator connections ONLY (there is no power inlet). Please note that there are no wattmeters to help you balance your loads on your generator, so your installer will have to accomplish the load balancing via the wiring at the time of installation.

Prewiring means it's faster to install!

Because it was designed with off-the-shelf circuit breakers you don't have to search high and low for replacements, and your installer can reconfigure the breaker combinations to suit your family's needs. UL Listed with Siemens, Square D (HOM), Cutler-Hammer (BR) and GE (THQL) breakers, and accommodates GFCI and Arc-fault breakers to meet 2008 code requirements.

Includes two 15-amp 1-pole breakers, two 20-amp 1-pole breakers, and one 2-pole 20 amp breaker. A 2-pole 60 amp breaker must be installed in existing load center (not included) to feed this switch. UL 1008 Listed. Protected by US Patent 6,861,596 B2 and other patents pending. Dimensions: 9.25 W x 11.125H x 3.375

D. Optional Flush Mounting Plate (Model 50329) available (sold separately). Use with Power inlet box models 14302 or 1430V.

Product Code: 3016
Weight: 13 lbs.

\$221.00

Helpful Links:
[Tell A Friend](#)

[Cancel Selection](#) ✕

[Order](#) ✓

May we recommend the following items?

Code	Name	Price	
50329	Flush Mounting Plate for Prewired Models 2026, 3028 and 3016	\$ 22.00	View Product

[Home](#) | [About Us](#) | [News & Press](#) | [Our Products](#) | [Specials & Sale Items](#) | [Clearance Items](#) | [Support](#) | [Locate A Dealer](#) | [Contact US](#) | [Dealer Login](#)

© 2006, GenTran Corporation. All Rights Reserved. **1.888.GEN.TRAN** | [Site Map](#)
Designed & Maintained By: [Bizography.com](#)