



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30171 Wire-Nut Wire Conn, Model 71B Gray, 1, 000/Box

Ideal

Catalog Number	30171
Manufacturer	Ideal
Description	Ideal, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 5, Conductor Range: 22 - 16 Awg, Min 2-16AWG Max 2-16AWG, Color: Gray, Material: Flame-Retardant Polypropylene, Voltage Rating: 300 V, Environmental Conditions: Tough, UI 94V-2 Flame-Retardant Shell Rated At 105 Deg C (221 F), Model Number: 71B, Flammability Rating: UI 94V-2
Weight per unit	1.2 (lbs/each)
Product Category	Electrical Fixture Conn (Nuts

Features

Material	Flame-Retardant Polypropylene
Number of Conductors	1 to 5
Voltage Rating	300

Material, Color, and Finish

Color	Gray
-------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	WIRE-NUT WIRE CONN, MODEL 71B GRAY, 1,000/BOX
extra long description	IDEAL 30-171 WIRENUT 71B GRAY, 1000
Features	The IDEAL Wire-Nut Wire Connector set new standards for innovation, quality and convenience when it was first introduced in 1928. As the first screw-on wire connector in America, it literally set the industry standard for years to come. With a fixed, square-wire spring and a positive grip shell, the Wire-Nut is perfect to twist-on with fingers for a secure connection that will last. The refined wire range makes it the best choice for fine stranded wire applications. The Wire-Nut also features a tough, flame
Long Description	IDEAL, Wire Connector, Wire-Nut, Twist-On, Number Of Conductors: 1 to 5, Conductor Range: 22 - 16 AWG, Min 2-16AWG MAX 2-16AWG, Color: Gray, Material: Flame-retardant polypropylene, Voltage Rating: 300 V, Environmental Conditions: Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F), Model Number: 71B, Flammability Rating: UL 94V-2
Product Type	Wirenut 71B Gray, 1000 Carton
Special Features	Features: Fixed, Square-Wire Spring Creates Its Own Threads Maintains A Secure Positive Grip That Will Not Relax Over Time; No Pre-Twisting Required Positive Grip Design Provides Fast, Easy Installation; Deep Skirt Helps Protect Against Flash-Over; Reusable For Easy Circuit Changes And Additions; Tough, UL94V-2 Flame-Retardant Shell Rated At 105 Degree C (221 Degree F); UL Listed To 486C And CSA Certified To C22.2 #188; Comply With Federal Specification W-S-610E; Model Number: 71B; Flammability Rating: UL

Manufacturer Information

Brand	Ideal
GTIN	00783250301713
Manufacturers Part Number	30-171
sub brand	Wire-Nut®
UPC	783250301713

Taxonomies, Classifications, and Categories

Category Description	Datacom Wiring Devices and Accessories
Type	Twist-On

Availability

minimum qty	1000
-------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1000
Weight Per each	1.2

Uses, Certifications, and Standards

Application	Insulating or Joining 2 or more conductors
environmental conditions	Tough, UL 94V-2 Flame-Retardant Shell Rated At 105 DEG C (221 F)
standard	CSA Certified to C22.2 #188, UL Listed to 486C, complies with Federal Specification W-S-610E