



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



30248SD Encl 30X24X8 N4 SLDHC, QTR TRN LTCH

Cooper B-Line/Cable Tray

Catalog Number	30248SD
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Wall Mounted Panel Enclosure, 30" Height, 8" Length, 24" Width, Nema 4, Hinged Cover, SD Enclosure, Wall Mount, Medium Single Door, Thru Holes, Optional External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket
Weight per unit	59.4 (lbs/each)
Product Category	Nema Types 4 & 12 Metallic Enc

Features

dimensions	8.0000 IN X 24.0000 IN X 30.0000 IN
Material	Carbon Steel
Mounting Type	Wall

Material, Color, and Finish

Color	ANSI 61 GRAY
-------	--------------

Dimensions and Weight

Size	24.00 In Width X 8.00 In Depth X 30.00 In Height
------	--

Descriptions

Description	ENCL 30X24X8 N4 SLDHC,QTR TRN LTCH
extra long description	B-LINE 30248-SD TYPE 4/12 SGL SOLID
Features	Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.
Long Description	Eaton B-Line series wall mounted panel enclosure,30" height,8" length,24" width,NEMA 4,Hinged cover,SD enclosure,Wall mount,Medium single door,Thru holes,optional external mounting feet,Carbon steel,Seamless poured in-place gasket
Product Type	Type 4/12 SGL Solid Door Enc, 30X24X8
Special Features	1/4 turn latches

Manufacturer Information

Brand	Eaton
GTIN	00782051091960
Manufacturers Part Number	30248-SD
UPC	782051091960

Taxonomies, Classifications, and Categories

Category Description	STEEL JUNCTION BOXES
Type	Wall mounted panel enclosure



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	59.371

Uses, Certifications, and Standards

Application	Datacenters - IT Space: CI and Hyper ConvergedCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherOther IT and Datacom - IT and Datacomm - OtherCommercial / Institutional Buildings / Structures - Power Distribution and ControlsCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsGeneration - Renewable Energy - Alternative EnergyCommercial / Institutional Buildings / Structures - Safety and Security SystemsCommercial / Ins
Mounting	WALL
nema rating	4
standard	UL 50,CSA C22.2.,NEMA