



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 30352J Powerplug Disconnect, Model 102, 2-Wire, 150/Jar *Ideal*

Catalog Number	30352J
Manufacturer	Ideal
Description	Ideal, Luminaire Disconnect, Powerplug, 2-Wire Standard Version, Wire Size: 12 - 18 Awg Solid, 12 - 14 Awg Stranded, 12 - 14, 16, 18 Awg Stranded Tin-Bonded, Voltage Rating: 600 V, Material: Nylon Housing, Copper Alloy Contacts, Amperage Rating: 6 Amp, Color: Orange, Model: 102
Weight per unit	0.0137 (lbs/each)
Product Category	Small Terminals & Connectors

### Features

amperage rating	6
Material	Nylon Housing, Copper Alloy Contacts
Voltage Rating	600
Wire Size	12 - 18 AWG Solid, 12 - 14 AWG Stranded, 12 - 14, 16, 18 AWG Stranded Tin-Bonded

### Material, Color, and Finish

Color	Orange
-------	--------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	POWERPLUG DISCONNECT, MODEL 102, 2-WIRE, 150/JAR
extra long description	IDEAL 30-352J POWERPLUG DISC 102, 1
Features	Patented push-in technology quickly locks wires in placeAllows for safe disconnect of hot and neutral ballast wiringBoth halves are touch-safe? per UL 2459Push-in technology results in quicker connections, saving time and increasing productivityFits through 1/2 in. knockoutKits available for all lighting installation and maintenance needsThe PowerPlug features patented IDEAL push-in technology that quickly locks wires in place. It helps reduce electrical shock hazard during ballast replacement by safely di
Long Description	IDEAL, Luminaire Disconnect, PowerPlug, 2-Wire Standard Version, Wire Size: 12 - 18 AWG Solid, 12 - 14 AWG Stranded, 12 - 14, 16, 18 AWG Stranded Tin-Bonded, Voltage Rating: 600 V, Material: Nylon Housing, Copper Alloy Contacts, Amperage Rating: 6 AMP, Color: Orange, Model: 102
Product Type	Powerplug Disc 102, 150 JR
Special Features	Features: Meets CEC And NEC Code Changes For Non-Residential Fluorescent Luminaires With Ballasts; Perfect For OEM Or Retrofit Lighting Applications; Patented Push-In Technology Quickly Locks Wires In Place; Passes UL 2459 & CSA 182.3 Finger Probe Requirements; Fits Through 1/2 In. Knockout; Pieces Pull Apart Safely And Easily; 3/8 In. Strip Length Indicator; Thumb Ridges Provide Superior Grip; Model: 102

## Manufacturer Information

Brand	Ideal
GTIN	00783250667864
Manufacturers Part Number	30-352J
sub brand	PowerPlug®
UPC	783250667864

## Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS
Type	2-Wire Standard Version

## Availability

minimum qty	150
-------------	-----

## Packaging

Carton	150
Package	900
Weight Per each	0.0137



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application	For 1-Ballast Fixture New Installations and Retrofits
standard	CSA, UL Listed, RoHS