

LENOX *DIAMOND* HOLE SAWS

More Holes. Less Time.

STANDARD HOLE SAWS

LONG LASTING

Brazed diamond edge for more holes in tile and stone

DURABLE

Robust design for greater durability in tough applications

FAST CUTTING

Cuts holes in less time than carbide grit or carbide tipped hole saws

EASIER PLUG REMOVAL


Round holes make removing plugs faster and easier

USE STANDARD ARBOR OR *SNAP-BACK™* ARBOR

1 PER PACK PROD NO	IN	MM	PIPE TAP		PIPE ENTRANCE		USE ARBOR	
			IN	MM	IN	MM	<i>SNAP-BACK</i>	STANDARD
1211314DGHS	7/8	22	3/4	19	1/2	13	5L	1L, 4L or 5L
1225618DGHS	1-1/8	29	1	25	3/4	19	5L	1L, 4L or 5L
1211520DGHS	1-1/4	32					2L, 6L	2L, 3L or 6L
1211722DGHS	1-3/8	35					2L, 6L	2L, 3L or 6L
1211824DGHS	1-1/2	38	1-1/4	32			2L, 6L	2L, 3L, 6L or 7L
1211932DGHS	2	51			1-1/2	38	2L, 6L	2L, 3L, 6L or 7L
1212040DGHS	2-1/2	64			2	51	2L, 6L	2L, 3L, 6L or 7L



Diamond Edge



Easier Plug Removal

CARBIDE GRIT RECESSED LIGHTING HOLE SAWS

Best for Cutting Abrasive Materials

LONG LIFE

Hard tungsten carbide grit edge for a long life in abrasive materials

FAST, EASY CUTTING

Continuous cutting edge for smooth cutting

LIMITS DUST/DEBRIS

Solid back design collects dust and debris

NEW DESIGN



1 PER BOX PROD NO	DIAMETER		FOR FIXTURES	USE ARBOR	
	IN	MM		<i>SNAP-BACK</i>	STANDARD
30861438RL	4-3/8	111	Capri, Marco & Halo, Mini-Juno	2L	2L
12100538RL	5-3/8	127	Capri, Marco & Halo, Mini-Juno, Lightolier & Halo	2L	2L
30862638RL	6-3/8	162	Capri, Halo, Pathway & Thomas	2L	2L
30863658RL	6-5/8	168	Juno, Progress & Pathway	2L	2L
30864678RL	6-7/8	175	Capri, Hubbell®, Lightolier®, Lithonia®, Marco, Prescolite®, Progress	2L	2L

Use 123CT or 4321 Pilot Drill

HALO is a registered trademark of Halo Lighting, JUNO is a registered trademark of Juno Lighting Inc., LITHONIA is a registered trademark of Lithonia, Inc., LIGHTOLIER is a registered trademark of Lightolier, Inc., and PRESCOLITE is a registered trademark of Prescolite, Inc.