

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4406 Highway 28 East 71360-0000, LA Pineville Phone: 318-767-0900 Fax: 318-767-0010



## 31012 Thumb Winder Fish Tape, 25' X 1/8", X .045" $_{\it Ideal}$

Catalog Number	31012	
Manufacturer	ldeal	
Description	Ideal, Fish Tape, Blued-Steel, Thumb -Winder, Length: 25 FT, Width: 1/8 In, Thickness: 045 In, Tensile Strength: 1600 LB, Tape End: Formed Hook, Material: Highest Grade Carbon Steel, Case Diameter: 7 In	
Weight per unit	0.9200 (lbs/each)	
Product Category	Fishing Equipment	
Features		
Material	Highest Grade Carbon Steel	
tape end	Formed Hook	
Tensile Strength	1600	
Dimensions and Weight		
Length	25	
Thickness	045	
Width	1/8	
Descriptions		
Description	THUMB WINDER FISH TAPE, 25' X 1/8", X .045"	
extra long description	IDEAL 31-012 Fish Tape,IDEAL,Blued-	
Features	Perfect for longer conduit runs, this fish tape boasts the highest tensile strength, and highest grade carbon steel for professional durability and reliability. The Blued-Steel also provides rust and corrosion resistance for longer life.	
Long Description	IDEAL, Fish Tape, Blued-Steel, Thumb -Winder, Length: 25 FT, Width: 1/8 IN, Thickness: 045 IN, Tensile Strength: 1600 LB, Tape End: Formed Hook, Material: Highest Grade Carbon Steel, Case Diameter: 7 IN	
Product Type	Fish Tape, Ideal, Blued-Steel, Thumb -Winder, 25.000 FT Len, 1/8	
Special Features	Features: Unique Finish Is Non-Oily And Resists Rust; Industry's Straightest Wire; Stiffer For Long Runs; Highest Grade Carbon Steel; Tensile Strength 1,600 LB; Multiple Options In Width, Length And Eyelet For Ease Of Use; Case Diameter: 7 IN	
Manufacturer Information		
Brand	ldeal	
GTIN	00783250310128	
Manufacturers Part Number	31-012	
UPC	783250310128	

4406 Highway 28 East 71360-0000, LA Pineville Phone: 318-767-0900 Fax: 318-767-0010

Taxonomies, Classifications, ar	nd Categories	
Category Description	HAND TOOLS	
Packaging		
Carton	1	
Weight Per each	0.92	