



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 31033 Tape-Pak Fish Tape, 50' X 1/8", X .060"

*Ideal*

|                  |   |
|------------------|---|
| Catalog Number   | 31033   |
| Manufacturer     | Ideal   |
| Description      | Ideal, Fish Tape, Blued-Steel, Tuff-Grip Pro, Length: 50 FT, Width: 1/8 In, Thickness: .060 In, Tensile Strength: 1600 LB, Tape End: Formed Hook, Material: Highest Grade Carbon Steel, Case Diameter: 9 In |
| Weight per unit  | 2.1 (lbs/each)  |
| Product Category | Fishing Equipment   |

### Features

|                  |                            |
|------------------|----------------------------|
| Material         | Highest Grade Carbon Steel |
| tape end         | Formed Hook                |
| Tensile Strength | 1600                       |

### Dimensions and Weight

|           |      |
|-----------|------|
| Length    | 50   |
| Thickness | .060 |
| Width     | 1/8  |

### Descriptions

|                        |  |
|------------------------|--|
| Description            | TAPE-PAK FISH TAPE, 50' X 1/8", X .060"  |
| extra long description | IDEAL 31-033 TUFF-GRIP-PRO 50FT, .12   |
| Features               | Perfect for longer conduit runs, this fish tape boasts the highest tensile strength, and highest grade carbon steel for professional durability and reliability. The Blued-Steel also provides rust and corrosion resistance for longer life. The Tuff-Grip Pro case and handle are impact resistant, while the unique design keeps the wire inside the case, even after a long fall. Multiple width, length and eyelet options are available for ease of use for any application. Replacement tapes also available. |
| Long Description       | IDEAL, Fish Tape, Blued-Steel, Tuff-Grip Pro, Length: 50 FT, Width: 1/8 IN, Thickness: .060 IN, Tensile Strength: 1600 LB, Tape End: Formed Hook, Material: Highest Grade Carbon Steel, Case Diameter: 9 IN  |
| Product Type           | Tuff-Grip-Pro 50FT, .125"X.06"   |
| Special Features       | Features: Laser Etched In 12 IN Increments To Provide Instant Conduit Length; Unique Finish Is Non-Oily And Resists Rust; Industry's Straightest Wire; Stiffer For Long Runs; Highest Grade Carbon Steel; Tensile Strength 1,600 LB; Multiple Options In Width, Length And Eyelet For Ease Of Use; Case Diameter: 9 IN   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                            |
|---------------------------|----------------------------|
| Brand                     | Ideal                      |
| GTIN                      | 00783250310333             |
| Manufacturers Part Number | 31-033                     |
| sub brand                 | Blued-Steel, Tuff-Grip Pro |
| UPC                       | 783250310333               |

## Taxonomies, Classifications, and Categories

|                      |            |
|----------------------|------------|
| Category Description | HAND TOOLS |
|----------------------|------------|

## Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 2.1 |