

E26 6" Trim Series


DESCRIPTION

Coilex® Baffle trim in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

- Black or white phenolic Coilex baffle with white metal trim ring
- Removable trim ring
- Accessories available: TRM6 designer trim rings, OT403 oversized trim ring
- Coil spring retention



Dimensions:

H: 3-1/16"[78mm]
OD: 7-1/4"[184mm]

Housings	Max Lamp Compatibility
H7ICT H7RICT	50W PAR30S, 75W PAR30L, 45W BR38, 65W BR30, 75W R30, 85W BR40
H7ICAT H7RICAT	50W PAR30S, 75W PAR30L, 45W PAR38, 65W BR30, 85W BR40
E7ICAT E7RICAT	75W PAR30S, 75W PAR30L, 90W PAR38, 65W BR30, 90W BR40, 75W R30, 100W R40
H7UICAT	75W PAR30S, 75W PAR30L, 90W PAR38, 65W BR30, 90W BR40, 75W R30, 100W R40
H27ICAT H27RICAT E27ICAT E27RICAT	50W PAR30S, 75W PAR30L, 65W BR30
H7T H7TCP H7RT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
E7TAT E7RTAT	75W PAR30S, 75W PAR30L, 65W BR30
H27T H27RT E27TAT E27RTAT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30

Compatible with Halogen, Incandescent, LED* or CFL* lamps.

ORDERING INFORMATION

SAMPLE NUMBER: 310W


Trim	Finish
310W= 6" White Baffle, White Trim	WH=White
310P= 6" Black Baffle, White Trim	WH=White
310SN= 6" Black Baffle, Satin Nickel Trim	SN=Satin Nickel
310TBZ= 6" Black Baffle, Tuscan Bronze Trim	TBZ=Tuscan Bronze

HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
30SBAT	Baffle	•	•	•	•	•	•	•	
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
				•	•	•	•		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•	•	•	•	•			•
		H27RT	E27TAT	E27RTAT					
		•	•	•					

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.


*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.



310W
White Trim, White Baffle



310P
White Trim, Black Baffle



310SN
Satin Nickel Trim, Black Baffle



310TBZ
Tuscan Bronze Trim, Black Baffle

310

6-Inch Coilex® Baffle

air ¹⁰/₁₀ *life*™

UL US
LISTED

For use in Halo listed housings.

CLASSIFIED
UL US

Select trims are classified for use in others housings.
See www.eaton.com/lighting/legal.

E26 6" Trim Series


DESCRIPTION

Coilex® Baffle trim in the 6" trim family for use in recessed downlighting. Compatible for use in Halo and other housings.

Catalog #		Type
Project		
Comments		Date
Prepared by		

SPECIFICATION FEATURES

- Black or white phenolic Coilex baffle with white metal trim ring
- Removable trim ring
- Accessories available: TRM6 designer trim rings, OT403 oversized trim ring
- Coil spring retention




Dimensions:

H: 3-1/16"[78mm]
OD: 7-1/4"[184mm]

Housings	Max Lamp Compatibility
H7ICT H7RICT	50W PAR30S, 75W PAR30L, 45W BR38, 65W BR30, 75W R30, 85W BR40
H7ICAT H7RICAT	50W PAR30S, 75W PAR30L, 45W PAR38, 65W BR30, 85W BR40
E7ICAT E7RICAT	75W PAR30S, 75W PAR30L, 90W PAR38, 65W BR30, 90W BR40, 75W R30, 100W R40
H7UICAT	75W PAR30S, 75W PAR30L, 90W PAR38, 65W BR30, 90W BR40, 75W R30, 100W R40
H27ICAT H27RICAT E27ICAT E27RICAT	50W PAR30S, 75W PAR30L, 65W BR30
H7T H7TCP H7RT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30
E7TAT E7RTAT	75W PAR30S, 75W PAR30L, 65W BR30
H27T H27RT E27TAT E27RTAT	75W PAR30S, 75W PAR30L, 65W BR30, 75W R30


Compatible with Halogen, Incandescent, LED* or CFL* lamps.



310W
White Trim, White Baffle



310P
White Trim, Black Baffle



310SN
Satin Nickel Trim, Black Baffle



310TBZ
Tuscan Bronze Trim, Black Baffle

310

6-Inch Coilex® Baffle

ORDERING INFORMATION

SAMPLE NUMBER: 310W

Trim	Finish
310W = 6" White Baffle, White Trim	WH =White
310P = 6" Black Baffle, White Trim	WH =White
310SN = 6" Black Baffle, Satin Nickel Trim	SN =Satin Nickel
310TBZ = 6" Black Baffle, Tuscan Bronze Trim	TBZ =Tuscan Bronze

HALO HOUSING COMPATIBILITY

Trim #	Style	H7ICT	H7ICAT	H7RICT	H7RICAT	E7ICAT	E7RICAT	H7UICAT	H7ICTNB
30SBAT	Baffle	•	•	•	•	•	•	•	
		H7ICATNB	E7ICATNB	H27ICAT	H27RICAT	E27ICAT	E27RICAT		
				•	•	•	•		
		H7T	H7TCP	H7RT	E7TAT	E7RTAT	H7TNB	E7TATNB	H27T
		•	•	•	•	•			•
		H27RT	E27TAT	E27RTAT					
		•	•	•					

For use in select other's housings, refer to U.L. classification list at www.eaton.com/lighting/legal.

*UL1993 listed LED & CFL equivalent lamps permitted. Consult lamp manufacturer for conditions of use. Eaton does not warranty the lamp.

air¹⁸⁰™

UL US
LISTED

For use in Halo listed housings.

CLASSIFIED
UL US

Select trims are classified for use in others housings.
See www.eaton.com/lighting/legal.