

## DESCRIPTION

Coilex® Baffle trim in the 6" trim family for use in recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

Black or white phenolic coilex baffle with separate metal ring. Uses coil spring retention. Trim available in a variety of finishes.

### Lamp Listings - Incandescent

H7T	65W BR30, 75W R30, 75W PAR30
H7TCP	
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L

H7ICAT	45W PAR38, 50W PAR30, 65W BR30, 75W R30, 75W PAR30L
H7ICT	
H7RICAT	
H7RICT	


H7UICAT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W PAR38, 90W BR40, 100W, R40
H7UICT	

### Lamp Listings - GU24


H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	

### Lamp Listings - Incandescent

H27ICAT	50W PAR30, 65W BR30, 75W PAR30L
H27ICT	
H27RICAT	
H27RICT	
H27RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L
H27T	




**310W, P, SN, TBZ**  
Height: 3-1/16" [78mm]  
Outside Diameter: 7-1/4" [184mm]




**310WG, PG**  
Height: 3-1/16" [78mm]  
Outside Diameter: 8" [203mm]

## ORDERING INFORMATION


Trim	Finish	Accessories
<input type="text"/>	<input type="text"/>	<input type="text"/>
<b>310</b> = 6" Coilex baffle	<b>W</b> = White trim ring with white baffle <b>P</b> = Black trim ring with black baffle <b>SN</b> = Satin nickel trim ring with black baffle <b>TBZ</b> = Tuscan bronze trim ring with black baffle	<b>OT403P</b> = 6" Oversize trim ring - white  <b>Designer/Replacement Trim Rings</b> <b>TRM6P</b> = 6" White metal <b>TRM6C</b> = 6" Chrome <b>TRM6SN</b> = 6" Satin nickel <b>TRM6TBZ</b> = 6" Tuscan bronze <b>TRM6MB</b> = 6" Black metal <b>TRM7MB</b> = 6" Black plastic




**310W**  
White Trim, White Baffle



**310P**  
White Trim, Black Baffle



**310SN**  
Satin Nickel Trim, Black Baffle



**310TBZ**  
Tuscan Bronze Trim, Black Baffle

## 310

6-Inch Coilex® Baffle

## DESCRIPTION

Coilex® Baffle trim in the 6" trim family for use in recessed downlighting.

Catalog #		Type
Project		
Comments		Date
Prepared by		

## SPECIFICATION FEATURES

Black or white phenolic coilex baffle with separate metal ring. Uses coil spring retention. Trim available in a variety of finishes.

### Lamp Listings - Incandescent

H7T	65W BR30, 75W R30, 75W PAR30
H7TCP	
H7RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L

H7ICAT	45W PAR38, 50W PAR30, 65W BR30, 75W R30, 75W PAR30L
H7ICT	
H7RICAT	
H7RICT	


H7UICAT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L, 90W PAR38, 90W BR40, 100W, R40
H7UICT	

### Lamp Listings - GU24


H724ICAT	CF15/R30/GU24
H724ICATL	
H724RICAT	CF13/GU24 (spiral)
H724RICATL	

### Lamp Listings - Incandescent

H27ICAT	50W PAR30, 65W BR30, 75W PAR30L
H27ICT	
H27RICAT	
H27RICT	
H27RT	65W BR30, 75W R30, 75W PAR30, 75W PAR30L
H27T	




**310W, P, SN, TBZ**  
Height: 3-1/16" [78mm]  
Outside Diameter: 7-1/4" [184mm]




**310WG, PG**  
Height: 3-1/16" [78mm]  
Outside Diameter: 8" [203mm]

## ORDERING INFORMATION


Trim	Finish	Accessories
<input type="text"/>	<input type="text"/>	<input type="text"/>
<b>310</b> = 6" Coilex baffle	<b>W</b> = White trim ring with white baffle <b>P</b> = Black trim ring with black baffle <b>SN</b> = Satin nickel trim ring with black baffle <b>TBZ</b> = Tuscan bronze trim ring with black baffle	<b>OT403P</b> = 6" Oversize trim ring - white  <b>Designer/Replacement Trim Rings</b> <b>TRM6P</b> = 6" White metal <b>TRM6C</b> = 6" Chrome <b>TRM6SN</b> = 6" Satin nickel <b>TRM6TBZ</b> = 6" Tuscan bronze <b>TRM6MB</b> = 6" Black metal <b>TRM7MB</b> = 6" Black plastic




**310W**  
White Trim, White Baffle



**310P**  
White Trim, Black Baffle



**310SN**  
Satin Nickel Trim, Black Baffle



**310TBZ**  
Tuscan Bronze Trim, Black Baffle

## 310

6-Inch Coilex® Baffle