



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



31381 ClearGlide Gallon Pail

Ideal

Catalog Number	31381
Manufacturer	Ideal
Description	Lubricant, 1 Gal Pail, Colorless, Slight Odor, ClearGlide Lubricant, 1.09 Specific Gravity, +40 to +100 °F, 8.58 LB
Weight per unit	8.6 (lbs/each)
Product Category	Tools - Paint, Chemicals, Etc.

Dimensions and Weight

Size	1 PH
------	------

Descriptions

Description	CLEARGLIDE GALLON PAIL
Special Features	Clear and colorless for quick and easy clean-up; Exceptional lubricity for super-fast pulls; Polymer-based formula perfect for all electrical and datacom applications; Safe to use with all cable types; Remains stable over wide temperature range; Dries to a semi-fluid film that won't clog conduit; Clings to cable throughout long pulls; Easy to apply by hand, brush, or pump; Environmentally safe - non-toxic, non-flammable, and non-corrosive

Manufacturer Information

Brand	IDEAL
GTIN	00783250348145
sub brand	ClearGlide
UPC	783250348145

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Lubricant

Packaging

Carton	1
Package	4
Weight Per each	8.575

Uses, Certifications, and Standards

standard	UL Listed
----------	-----------

ClearGlide™ Wire Pulling Lubricant

- Clear and colorless for quick and easy clean-up – great for indoor and retrofit pulls
- Exceptional lubricity for super-fast pulls
- Polymer-based formula is perfect for all electrical and datacomm applications
- Safe to use with all cable types
- Controlled evaporation rate is ideal for shorter runs
- Remains stable over wide temperature range – usable from 30°F to 180°F (-1°C to 82°C)
- Dries to a semi-fluid film that won't clog conduit
- Easy to apply by hand, brush or pump
- Environmentally safe – non-toxic, non-flammable and non-corrosive



Description	Cat. No.
1-qt. Squeeze bottle	31-388
1-gal. Bucket	31-381
5-gal. Bucket	31-385
5-gal. Bucket – 36 Buckets/Pallet	31-385BP
55-gal. Drum	31-2143



Velocity™ Wire Pulling Lubricant

- High cling factor
- Maximum friction reduction
- Specification grade
- Compatible with all popular cable types
- Temperature stable
- UL listed
- Non-combustible residue
- Environmentally safe -- non-toxic, non-flammable and non-corrosive



Description	Cat. No.
1-qt. Squeeze bottle	31-276
1-gal. Bucket	31-277
5-gal. Bucket	31-278
5-gal. Bucket – 36 Buckets/pallet	31-278BP
55-gal. Drum	31-279
1-qt. Bag (12 bags/bucket)	31-282
1/2-gal. Bag (6 bags/bucket)	31-283



Recommended Qty. of Lubricant Formula

$$Q = .0015 \times L \times D$$

Q = Quantity of recommended lube in gallons

L = Length of pull in feet

D = Nominal ID of conduit in inches

The formula listed above is used as a guideline on estimating the quantity of lube needed for various jobs. Many factors go into a cable pull, however this formula is just based on length of the pull and diameter of the conduit.

Increase quantities for the following troubles:

- Stiff, heavy cable
- Pulls with several bends
- Rough, old or dirty conduits
- High temperatures
- High percent conduit fill

Selection & Application Guides

Description	Cat. No.
Lubricant Selection Slide Rule	P-2710

Web Based Selection & Application Guide:
<http://ideal.sdafiles.com/#select>

