



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

15152 E Fremont Dr
80112-0000, CO Centennial
Phone: 720-278-7555
Fax: 720-259-8851



324 400A Ac True RMS Clamp Meter W/Temp

Fluke Electronics

Catalog Number	324
Manufacturer	Fluke Electronics
Description	1 RMS Clamp Meter, Model: 324 Series, Voltage Rating: 600 Vac/VDC, Amperage Rating: 40 - 400 Amp, Resistance: 400 - 4000 Ohm, Capacitance: 100 - 1000 MFD, Accuracy: 1.5 PCT Plus/Minus 5 Digits (45 - 400 HZ) For Ac Current, 1.5 PCT Plus/Minus 5 Digits For Ac Voltage, 1 PCT Plus/Minus 5 Digits For DC Voltage, 1 PCT Plus/Minus 5 Digits Resistance, Display: Large, Temperature Rating: -10 to 400 Deg C Contact Temperature, Peak Hold: Yes, Dimensions: 207 In Height X 75 In Width X 34 In Depth, Continuity: Less TH
Weight per unit	1.6 (lbs/each)
Product Category	Test Equipment - Multimeters

Features

Voltage Rating	600 V
----------------	-------

Descriptions

Description	400A AC TRUE RMS CLAMP METER W/TEMP
extra long description	FLK FLUKE-324 TRUE RMS CLP M 324 SE
Long Description	1 RMS Clamp Meter, Model: 324 Series, Voltage Rating: 600 VAC/VDC, Amperage Rating: 40 - 400 AMP, Resistance: 400 - 4000 OHM, Capacitance: 100 - 1000 MFD, Accuracy: 1.5 PCT Plus/Minus 5 Digits (45 - 400 HZ) For AC Current, 1.5 PCT Plus/Minus 5 Digits For AC Voltage, 1 PCT Plus/Minus 5 Digits For DC Voltage, 1 PCT Plus/Minus 5 Digits Resistance, Display: Large, Temperature Rating: -10 To 400 DEG C Contact Temperature, Peak Hold: Yes, Dimensions: 207 IN Height X 75 IN Width X 34 IN Depth, Continuity: Less Th
Product Type	True RMS CLP M 324 Series

Manufacturer Information

Brand	FLUKE
GTIN	00095969623759
Manufacturers Part Number	FLUKE-324
UPC	095969623759

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
----------------------	---

Packaging

Carton	1
Weight Per each	1.58



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

15152 E Fremont Dr
80112-0000, CO Centennial
Phone: 720-278-7555
Fax: 720-259-8851

Uses, Certifications, and Standards

Enclosure	Hard plastic
Operating Temperature	-10 °C to +50 °C