



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

3232TRWR TR WR Duplex Recp 15A 125V BN

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | 3232TRWR |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Duplex Receptacle, 15 A, 125 V, 2 Poles, 3 Wires, #14 to #12 Awg Compatible Wire Size, Side Wire;Push Wire Connection, Wall Mount, 1.320 In Length, 1.0 In Width, 4.20 In Height, Thermoplastic, Brown, Weather Resistant;Tamper Resistant, Impact Resistant, 0.1400 LB |
| Weight per unit | 0.1352 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 15 |
| connection | Side wire, push wire |
| indoor/outdoor | Outdoor |
| Outlet Type | Weather-Resistant, Tamper-Resistant |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wall Plate Included | NO |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 14 - 12 |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | TR WR DUPLEX RECP 15A 125V BN |
| extra long description | P&S 3232TRWR TR WR DUP REC 15A/125V |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007241747 |
| Manufacturers Part Number | 3232TRWR |
| UPC | 785007241747 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------|
| Category Description | Residential receptacles |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 200 |
| Weight Per each | 0.1352 |

Uses, Certifications, and Standards

| | |
|--------------------------|--------------------------------------|
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| standard | CULUS, cULus UL498, CSA C22.2 No. 42 |