ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
110 Success Blvd
Dumas, TX 79029-0000
Phone: 8069344805
Fax: 8067172052



327 2-1/2" PLASTIC BUSHING

NSI INDUSTRIES

Catalog Number	327
Manufacturer	NSI INDUSTRIES
Description	Plastic Bushing, 2-1/2 in Trade Size, Gray, Insulated, Straight Connection Orientation, Threaded Connection, 3-1/8 in Width, 5/8 in Height, 3-1/8 in Diameter, +150 °C Operating Temperature, 0.0475 lb/EA
Weight per unit	0.0475 (lbs/each)
Product Category	Plastic

Features

Material	Plastic
Media	Yes

Material, Color, and Finish

Color	Gray
Finish	NO FINISH

Dimensions and Weight

Size	2-1/2

Descriptions

Description	2-1/2" PLASTIC BUSHING
Long Description	Bushing, Plastic - 105 Degrees C, Size 2 1/2 Inch
Product Type	2-1/2 In Plastic Bushing 105C, Box Of 25
Special Features	Rounded surface of bushing prevents damage to wire insulation
Extra Long Description	BPT 327 2-1/2 IN Plastic Bushing 10

Manufacturer Information

Brand	Bridgeport
	Nsi Industries
GTIN	00781747003270
UPC	884739

Taxonomies, Classifications, and Categories

Category Description	COUPLINGS, ADAPTERS, REDUCERS, BUSHINGS, & CAPS
Type	BUSHING

Trade Size

Trade Size	2.5

Packaging

Carton	25
Weight Per Each	0.0475 (lbs/each)

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
110 Success Blvd
Dumas, TX 79029-0000
Phone: 8069344805
Fax: 8067172052

Uses, Certifications, and Standards

Application	Used with locknut to terminate threaded rigid and IMC to box, or used with connector to prevent damage to wire insulation. Rated 105 degree C.
Temperature Rating	105?°C
Standard	UL


Bridgeport Fittings Inc.
705 Lordship Blvd.
Stratford, CT 06615

Phone: 203-377-5944
Fax: 203-381-3488

Plastic - 105 C

Images





Download Photo Image Download Dimensional Image

Dimension A in Inches:	3-1/8
Dimension B in Inches:	5/8
Dimension C in Inches:	2-3/8

Application

Used with locknut to terminate threaded rigid and IMC to box, or used with connector to prevent damage to wire insulation. Rated 105 degree C.

Product Information

Material:	Plastic
Finish:	Plain

Certifications & Codes:

Federal Specification Number:	A-A-50553
NEMA Standard:	FB-1
UL File Number:	E9391
UL Standard:	UL-514B
UNSPSC:	39121312

Catalog ID: 327

UPC Number: 781747003270

Description: Bushing, Plastic - 105 Degrees C, Size 2 1/2 Inch

Application: Used with locknut to terminate threaded rigid and IMC to box, or used with connector to prevent damage to wire insulation. Rated 105 degree C.

Trade Size: 2-1/2"

Country of Manufacture: USA

Std Pkg Qty: 25

Unit Qty: Bulk