

XT COBALT STEP BITS

MAXIMUM LIFE IN STAINLESS STEEL



FAST

New split point tip penetrates
10GA stainless steel in
10 seconds

INNOVATIVE

Dual-flute design makes for
faster drilling with less force

DURABLE

Cobalt High Speed Steel
maximizes heat and
abrasion resistance



MADE FOR THE TRADE!™



DUAL-FLUTE

Two cutting edges share the load resulting in faster drill times with less force



COBALT HSS

Engineered for maximum life on stainless steel

30008C

34403C

34401C

STEAM OXIDE FINISH

Runs cooler and extends the life of the bit

NEW SPLIT POINT TIP

Eliminates walking and penetrates quickly

CUTS CLEAN, SMOOTH HOLES

SPECIFICATIONS

Stainless Steel Capacity Up to 10GA

Accessories..... Greenlee 462 Series Cutting Oil

Also cuts mild steel, copper, brass, aluminum, fiberglass, plastic, wood and laminates

CAT. NO.	# STEPS	MIN DIAMETER	INCREMENTS	MAX DIAMETER	HEX SHANK
34401C	13	1/8"	1/32"	1/2"	3/8"
34403C	12	3/16"	1/16"	7/8"	3/8"
30008C	3	1/2"	-	1-1/8"	3/8"
35884C	Includes all 3 step bit sizes in a case				

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
34401C	05789	XT Cobalt Step Bit, 1/2"
34403C	05790	XT Cobalt Step Bit, 7/8"
30008C	05792	XT Cobalt Step Bit, 1-1/8"
35884C	05793	XT Cobalt Step Bit, 1/2", 7/8", 1-1/8"



www.greenlee.com MA6439 08/15
 4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
 ©2015 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
 Greenlee Textron Inc. is a subsidiary of Textron Inc.

XT COBALT STEP BITS

MAXIMUM LIFE IN STAINLESS STEEL



FAST

New split point tip penetrates
10GA stainless steel in
10 seconds

INNOVATIVE

Dual-flute design makes for
faster drilling with less force

DURABLE

Cobalt High Speed Steel
maximizes heat and
abrasion resistance



MADE FOR THE TRADE!™



DUAL-FLUTE

Two cutting edges share the load resulting in faster drill times with less force



COBALT HSS

Engineered for maximum life on stainless steel

30008C

34403C

34401C



STEAM OXIDE FINISH

Runs cooler and extends the life of the bit

NEW SPLIT POINT TIP

Eliminates walking and penetrates quickly

CUTS CLEAN, SMOOTH HOLES

SPECIFICATIONS

Stainless Steel Capacity Up to 10GA

Accessories..... Greenlee 462 Series Cutting Oil

Also cuts mild steel, copper, brass, aluminum, fiberglass, plastic, wood and laminates

CAT. NO.	# STEPS	MIN DIAMETER	INCREMENTS	MAX DIAMETER	HEX SHANK
34401C	13	1/8"	1/32"	1/2"	3/8"
34403C	12	3/16"	1/16"	7/8"	3/8"
30008C	3	1/2"	-	1-1/8"	3/8"
35884C	Includes all 3 step bit sizes in a case				

ORDERING INFORMATION

CAT. NO.	UPC NO.	DESCRIPTION
34401C	05789	XT Cobalt Step Bit, 1/2"
34403C	05790	XT Cobalt Step Bit, 7/8"
30008C	05792	XT Cobalt Step Bit, 1-1/8"
35884C	05793	XT Cobalt Step Bit, 1/2", 7/8", 1-1/8"



www.greenlee.com MA6439 08/15
4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070
©2015 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA
Greenlee Textron Inc. is a subsidiary of Textron Inc.