



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



35988 Ratch-A-Nut 9-In-1 Screwdriver

Ideal

Catalog Number	35988
Manufacturer	Ideal
Description	Ratch-A-Nut 9-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: 1/4 In and 3/16 In Slotted, #1 and #2 Phillips, 1/4 In, 5/16 In, 7/16 In Nutdrivers, Ratcheting Screwdriver End, Ratcheting Wire Connector Wrench
Weight per unit	0.7000 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Handle Type	Textured, Ergonomic, Slip Resistant Comfort-Grip
-------------	--------------------------------------------------

Material, Color, and Finish

Blade Material	Chrome Vanadium
Handle Material	SANTOPRENE



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	RATCH-A-NUT 9-IN-1 SCREWDRIVER
extra long description	IDEAL 35-988 Screwdriver,Ideal,Ratc
Features	Patented Wire Connector Wrench accepts a wide variety of connectors and reduces finger fatiguePro-quality, 28 tooth, all metal ratchet can handle 225 lbs. of torque without failureErgonomic, slip-free textured grip provides excellent torque and is impervious to perspiration, gas, oil and chemicalsAccepts Twist-a-Nut replacement bitsBits included: 1/4 in. Slotted, 3/16 in. Slotted, #1 Phillips, #2 Phillips, 1/4 in. Nutdriver, 5/16 in. Nutdriver, and 7/16 in. NutdriverRatch-a-Nut 9-in-1 Screwdriver includes
Long Description	Ratch-a-Nut 9-In-1 Screwdriver, Textured, Ergonomic, Slip Resistant Comfort-Grip Handle, Santoprene Handle, Chrome Vanadium Blade, Includes: 1/4 IN And 3/16 IN Slotted, #1 And #2 Phillips, 1/4 IN, 5/16 IN, 7/16 IN Nutdrivers, Ratcheting Screwdriver End, Ratcheting Wire Connector Wrench
Product Type	Screwdriver, Ideal, Ratch-A-Nut
Special Features	Ratcheting wire connector wrench prevents finger fatigue and gets in tight spots; Premium screwdriver ratchet mechanism can handle high torque without failure; Ergonomic, slip resistant comfort-grip; Textured Santoprene grip provides excellent torque and resists perspiration, water, oil and chemicals; Accepts Twist-a-Nut replacement bits; Pro-quality, 28 tooth double action, twin-tooth ratchet; 225 LB of torque (stronger than human wrist can torque)

Manufacturer Information

Brand	Ideal
GTIN	00783250605224
Manufacturers Part Number	35-988
sub brand	Ratch-a-Nut
UPC	783250605224

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	9-In-1 Screwdriver

Packaging

Carton	1
Weight Per each	0.7