

# Eaton 3BR1224B100R

Catalog Number: 3BR1224B100R

Eaton BR main breaker loadcenter, No feed-thru lugs, Main circuit breaker, 100 A, C1r, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 24 Circuits, 12 Spaces, Four-wire, Three-phase, #4-1/0 AWG Cu/Al, Type BR 1-inch breakers, 208 Y/120, 240 V

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	3BR1224B100R
<b>UPC</b>	<b>Product Length/Depth</b>
786676440158	5.19 in
<b>Product Height</b>	<b>Product Width</b>
21 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
23 lb	10 year
<b>Certifications</b>	<b>Catalog Notes</b>
UL 50 UL 67	Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached, the maximum rating of the panel is the main breaker rating when used as service entrance equipment.



## Product specifications

### Number of spaces

12

### Special features

No feed-thru lugs

### Interrupt rating

10 kAIC

### Phase

Three-phase

### Wire size

#4-1/0 AWG Cu/Al

### Bus material

Aluminum

### Main circuit breaker

BR

### Enclosure

NEMA 3R

### Amperage Rating

100 A

### Enclosure material

Metallic

### Type

Main circuit breaker

### Cover

Cover included

### Used with

Type BR 1-inch breakers

### NEMA rating

NEMA 3R

### Number of wires

4

### Number of circuits

24

### Voltage rating

208Y/120, 240V

## Resources

### Brochures

Loadcenters and Circuit Breakers

Type BR 3-Phase Loadcenters

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, BR MAIN BREAKER, OUTDOOR NEMA 3R, 120/240 VAC, 3 PHASE

### Specifications and datasheets

3-Phase Loadcenter Program

Eaton Specification Sheet - 3BR1224B100R

Box size

C1R



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)