



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.
75119-0000, TX Ennis
Phone: 972-875-3413
Fax: 972-875-3174

3BR3042BC200R 3PH BR 30 Space 42 CKT 200A LC N3R Cu Bus

Eaton Corp

Catalog Number	3BR3042BC200R
Manufacturer	Eaton Corp
Description	Eaton BR Main Breaker Loadcenter, Main Circuit Breaker, 200 A, L1R, Copper, Nema 3R, 10 Kaic, CC, 42 Circuits, 30 Spaces, Four-Wire, Three-Phase, #6-4/0 Awg, Nema 3R
Weight per unit	51.5 (lbs/each)
Product Category	20250624133545

Dimensions and Weight

Depth	5
Height	39
Width	14.31

Descriptions

Description	3PH BR 30 SPACE 42 CKT 200A LC N3R CU BUS
extra long description	ETN 3BR3042BC200R 3 Ph/BR LC 200A M
Features	Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers protect the wires leading to individual electrical loads such as fixtures and outlets.
Long Description	Eaton BR main breaker loadcenter, Main circuit breaker, 200 A, L1R, Copper, NEMA 3R, 10 kAIC, CC, 42 Circuits, 30 Spaces, Four-wire, Three-phase, #6-4/0 AWG, NEMA 3R
Product Type	3 PH/BR LC 200A MCB 30/42 CKT Cu Bus

Manufacturer Information

Brand	Eaton
GTIN	00786689972387
Manufacturers Part Number	3BR3042BC200R
UPC	786689972387

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Main breaker loadcenter

Packaging

Carton	1
Weight Per each	51.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.
75119-0000, TX Ennis
Phone: 972-875-3413
Fax: 972-875-3174

Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional
EnergyMarine Vessels and Equipment - Marine Vessels and
Equipment - OtherDatacenters - IT Space: CI and Hyper
ConvergedGeneration - Renewable Energy - Alternative Energy

standard

UL 50,UL 67