

# Eaton 3BR1836L200

Catalog Number: 3BR1836L200

Eaton BR main lug loadcenter, No feed-thru lugs, Main lug, 200 A, C4, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, BWH, Combination, 36 Circuits, 18 Spaces, Four-wire, Three-phase, Type BR 1-inch breakers, 208 Y/120, 240 V, #1 AWG-300 kcmil Cu/Al



## General specifications

|                              |   |
|------------------------------|---|
| <b>Product Name</b>          | <b>Catalog Number</b>   |
| Eaton BR main lug loadcenter | 3BR1836L200   |
| <b>UPC</b>                   | <b>Product Length/Depth</b>   |
| 786676442053                 | 3.88 in   |
| <b>Product Height</b>        | <b>Product Width</b>  |
| 21 in                        | 14.31 in  |
| <b>Product Weight</b>        | <b>Warranty</b>   |
| 25.4 lb                      | 10 year   |
| <b>Certifications</b>        | <b>Catalog Notes</b>  |
| UL 67<br>UL 50               | Suitable for use as service equipment when no more than 6 main disconnecting means are provided or when not used as lighting & appliance panelboard |

## defaultTaxonomyAttributeLabel

### Special features

No feed-thru lugs

### Type

Main lug

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BWH

### Mounting

Combination

### Number of circuits

36

### Number of spaces

18

### Phase

Three-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

208Y/120, 240V

### Wire size

#1 AWG-300 kcmil Cu/Al

### Box size

C4

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - BR 1 LOADCENTER, MAIN LUG ONLY, INDOOR  
NEMA 1, 120/240 VAC, 3 PHASE

### Specifications and datasheets

Eaton Specification Sheet - 3BR1836L200

3-Phase Loadcenter Program

NEMA rating

NEMA 1

Number of wires

4



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)