

Eaton 3MM412RRL

Catalog Number: 3MM412RRL

Eaton's Three-Phase Residential Meter Stack Module, Group Metering Type, 125A, Aluminum Bus 800 Ampere, No bypass, Indoor/outdoor, Five-jaws, 4 Sockets, Three-phase in, single-phase out, Ringless Security, 120/208V



General specifications

Product Name	Catalog Number
Eaton residential meter stack	3MM412RRL
UPC	Product Length/Depth
786849052157	54.5 in
Product Height	Product Width
8 in	15 in
Product Weight	Warranty
61 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Type

Group Metering

Utility approvals

ME : Central Maine Power

NC : Dominion

VA : Dominion

ME : Emera Maine (Bangor Hydro Electric Co./ Maine Public Service Company)

AR : Entergy

LA : Entergy

MS : Entergy

TX : Entergy

GA : Georgia Power

KS : Kansas City Power and Light (KCPL) / Westar Energy

MO : Kansas City Power and Light (KCPL) / Westar Energy

TN : Middle Tennessee EMC

FL : Tallahassee City Electric

SC : South Carolina Electric and Gas (SCE&G)

IN : Indiana Michigan Power (IMP) (AEP East)

MI : Indiana Michigan Power (IMP) (AEP East)

OH : AEP Ohio (AEP East)

TN : Appalachian Power (AEP East)

VA : Appalachian Power (AEP East)

WV : Appalachian Power (AEP East)

TX : Texas-New Mexico Power (TNMP)

NM : Texas-New Mexico Power (TNMP)

Interrupt rating

Depends on selected main circuit breaker

Enclosure

Indoor/outdoor

Secondary circuit breaker

BR2_, BRH2_, BRHH2_

Bus Rating

800 A

Phase

Three-phase in, single-phase out

Voltage rating

120/208V

Amperage Rating

125A

Resources

Catalogs

Eaton's Volume 1—Residential and Light Commercial

Drawings

Dimensional Drawing - METER MODULES, DIMENSIONS, 125A, MM, TMP

Specifications and datasheets

Eaton Specification Sheet - 3MM412RRL

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services

Bus material

Aluminum

Bypass

None

Number of jaws

Five-jaw

Number of sockets

4

Phase balance

A-B

Security

Ringless



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)