

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



44102 Wire Marker BKLT, Asst A-Z, 0-15, +, -, /, 10 Each *Ideal*

Catalog Number	44102
Manufacturer	Ideal
Description	Ideal, Wire Marker Booklet, Size: 1/4 X 1-1/2 In Marker, Material: Plastic-Impregnated Cloth, Legend: A-Z, 0-15, +, , /, Temperature Rating: -40 to 180 Deg F, Markers Per Page: 10, Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 Oz/In Width Ultimate, Includes: 450 Wire Markers and 450 Terminal Markers
Weight per unit	0.1400 (lbs/each)
Product Category	Markers & Marking Tapes
Features	
Legend	A-Z, 0-15, +, , /
Material	Plastic-Impregnated Cloth
Number of Pages	10/Booklet
Material, Color, and Finish	
Legend Color	Non-Smear Black
Dimensions and Weight	
Size	1/4 X 1-1/2 IN Marker



ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

_		•		
	SCr	'n	TIA	nc
	. ~ I			
-	,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,,			

Descriptions			
Description	WIRE MARKER BKLT, ASST A-Z, 0-15, +, -, /, 10 EACH		
extra long description	IDEAL 44-102 Wire Marker Booklet,Id		
Features	Convenient pocket-size bookletsPlastic, cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilPerforated 1/4 in. x 1-1/2 in. markers can be separated into half-length sizesNon-smear black legendSelf-sticking on wire and cableFor applications above or below groundTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate		
Long Description	IDEAL, Wire Marker Booklet, Size: 1/4 X 1-1/2 IN Marker, Material: Plastic-Impregnated Cloth, Legend: A-Z, 0-15, +, , /, Temperature Rating: -40 To 180 DEG F, Markers Per Page: 10, Number Of Pages: 10/Booklet, Legend Color: Non-Smear Black, Adhesion: 45 OZ/IN Width Ultimate, Includes: 450 Wire Markers And 450 Terminal Markers		
Product Type	Wire Marker Booklet, Ideal, SZ: 1/4 X 1-1/2 In MRKR, Plastic-Im		
Special Features	Features: Convenient Pocket-Size Booklets; Plastic-Impregnated Cloth Construction For Long-Lasting Durability; Resists Abrasion, Moisture, Dirt And Oil; Perforated 1-1/2 IN Markers Can Be Separated Into Half-Length Sizes; Self-Sticking On Wire And Cable; Non-Smear Black Legend Ensures High Visibility; For Applications Above Or Below Ground; Ten Pages Per Booklet, 10 Markers Per Legend; Adhesion: 45 OZ/IN Width Ultimate; Includes: 450 Wire Markers And 450 Terminal Markers		
Manufacturer Information			
Brand	Ideal		
GTIN	00783250441020		
Manufacturers Part Number	44-102		
UPC	783250441020		
Taxonomies, Classifications, and Cate	egories		
Category Description			
Packaging Carton	1		
Package	5		
Weight Per each	0.14		
Uses, Certifications, and Standards			
standard	RoHS		
Temperature Rating	-40 To 180		