



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

277/480 VOLTS

44298 Voltage & Conduit Marker, "277/480V", Large, 1/Card *Ideal*

Catalog Number	44298
Manufacturer	Ideal
Description	Ideal, Marker Card, Voltage and Conduit, Large, Size: 2-1/4 In Width, Length: 9 In, Material: Vinyl-Impregnated Cloth, Legend: 277/480V, Temperature Range: -40 to 180 Deg F, Text Size: 1-3/4 In, Adhesion: 45 Oz/In Width Ultimate
Weight per unit	0.1240 (lbs/each)
Product Category	Markers & Marking Tapes

Features

Legend	277/480V
Material	Vinyl-Impregnated Cloth
Number of Markers	5

Dimensions and Weight

Length	9
Size	2-1/4 IN Width
Width	2-1/4

Descriptions

Description	VOLTAGE & CONDUIT MARKER, "277/480V", LARGE, 1/CARD
extra long description	IDEAL 44-298 Marker Card, Ideal, Volt
Features	Identify junction boxes, switches, circuit breakers, raceways, pipe and fuse boxesNon-conductive for user safetyHigh-adhesion properties with easy removabilityVinyl-impregnated cloth construction for long-lasting durabilityResist abrasion, moisture, dirt and oilNon-smear, black legend on bright orange background for high visibilityTemperature Range: -40°F to 180°F (-40°C to 82°C)Adhesion: 45 oz./in. width ultimate SELECT PART N
Long Description	IDEAL, Marker Card, Voltage And Conduit, Large, Size: 2-1/4 IN Width, Length: 9 IN, Material: Vinyl-Impregnated Cloth, Legend: 277/480V, Temperature Range: -40 to 180 DEG F, Text Size: 1-3/4 IN, Adhesion: 45 OZ/IN Width Ultimate
Product Type	Voltage & Conduit Marker, "277/480V", Large, 1/Card
Special Features	Features: Identify Junction Boxes, Switches, Circuit Breakers, Raceways, Pipe And Fuse Boxes; Non-Conductive For User Safety; High-Adhesion Properties With Easy Removability; Vinyl-Impregnated Cloth Construction Provides Long-Lasting Durability; Resist Abrasion, Moisture, Dirt And Oil; Non-Smear, Black Legend On Bright Orange BackgroundFor High Visibility; Temperature Range: -40 DEGF To 180 DEGF (-40 DEGC To 82 DEGC) Adhesion: 45 Oz/IN Width Ultimate; Temperature Range: -40 to 180 DEG F; Text Size: 1-3/4 IN



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Ideal
GTIN	00783250442980
Manufacturers Part Number	44-298
UPC	783250442980

Taxonomies, Classifications, and Categories

Category Description	WIRE LUBE, MARKERS, & TIES
Type	Voltage And Conduit, Large

Packaging

Carton	25
Weight Per each	0.124

Uses, Certifications, and Standards

standard	RoHS
----------	------