



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 461 3/4" Emt STL SS Coupling

*Crouse-Hinds*

Catalog Number	461
Manufacturer	Crouse-Hinds
Description	Emt Set Screw Coupling, 3/4 In Trade Size, Zinc Plated, 1.875 In Length, 0.11 LB/Ea
Weight per unit	0.1100 (lbs/each)
Product Category	Steel Set Screw Emt Couplings

### Features

Material	ZINC PLATED STEEL
----------	-------------------

### Descriptions

Description	3/4" EMT STL SS COUPLING
-------------	--------------------------

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564104618
UPC	784564104618

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	SET SCREW

### Packaging

Carton	25
Weight Per each	0.11

### Uses, Certifications, and Standards

standard	UL, cUL
----------	---------

# Thin Wall Conduit Fittings (for EMT Conduit)

## Set Screw Type Fittings – Steel

EMT Fittings

### SET SCREW TYPE FITTINGS

#### Features:

- Tri-head screws may be installed using a slotted, Phillips or Robertson head screwdriver
- Male hub threads – NPSM
- Steel locknuts
- Heavy steel walls
- Standard material: steel
- Standard finish: zinc plated
- Concrete tight when taped

#### Straight Connectors – Insulated

UL File No. E-22132



1450

1456



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
1450	1/2"	50	9
1451	3/4"	25	14
1452	1"	20	23
1453*	1 1/4"	10	46
1454*	1 1/2"	10	50
1455*	2"	5	78
1456*†	2 1/2"	2	130
1457*†	3"	1	140
1458*†	3 1/2"	1	180
1459*†	4"	1	225

\*Two tightening screws.  
†UL and cUL Listed for EMT, IMC and rigid conduit.

#### Straight Connectors – Non-insulated

UL File No. E-22132



450S

456



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
450S	1/2"	50	9
451	3/4"	25	15
452	1"	20	23
453*	1 1/4"	10	46
454*	1 1/2"	10	50
455*	2"	5	77
456*†	2 1/2"	2	130
457*†	3"	1	140
458*†	3 1/2"	1	180
459*†	4"	1	225

\*Two tightening screws.  
†UL and cUL Listed for EMT, IMC and rigid conduit.

#### Couplings

UL File No. E-22132



460

466



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
460	1/2"	50	9
461	3/4"	25	16
462	1"	20	23
463*	1 1/4"	10	42
464*	1 1/2"	10	50
465*	2"	5	77
466*†	2 1/2"	2	130
467*†	3"	1	140
468*†	3 1/2"	1	240
469*†	4"	1	250

\*Four tightening screws.  
†UL and cUL Listed for EMT, IMC and rigid conduit.

### Available in 7 Colors

Crouse-Hinds series painted EMT fittings consists of set screw, compression, insulated and non-insulated EMT fittings. Although red is the most commonly used, other colors offered include white, blue, green, yellow, black, and orange. These can also be used in architectural design, to better match look and feel to suit architectural specification and preference.



Red White Blue Yellow Orange Green Black

#### Part Number Example:

**450SGreen**

Non-insulated Set Screw Connector		Color
1/2"	450S	Red
3/4"	451	White
1"	452	Blue
1 1/4"	453	Yellow
1 1/2"	454	Orange
2"	455	Green
2 1/2"	456	Black
3"	457	
3 1/2"	458	
4"	459	

To order, simply add the name of the color needed after the catalog number.