






Catalog Number: 464-SC1
Item Description: N1 SCREW COVER ENCL
UPC Code: 784572107045

Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG NO. | LABEL NO. |
|----------------|-----------|
| 464-SC1-() | 1002135 |
| RC-464-SC1-() | 1125021 |
| SPSC-644() | 1132714 |



NOTES:



- 1.) BAG ASSY TO BE SHIPPED INSIDE OF ENCLOSURE.

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|--------------------------|
| 1 | 1 | (SEE CHART) | BACK WELDMENT |
| 2 | 1 | (SEE CHART) | COVER PLATE |
| 3 | 2 | 1001290 | SCREW, 10-32 X 5/16 |
| 4 | 1 | (SEE CHART) | LABEL (UL) |
| 5 | 1 | 1002475 | BAG ASSY (GROUND SCREW) |
| 6 | 0.25 | 1002937 | CARTON 4-PER (NOT SHOWN) |

| SUFFIX | FINISH | WELDMENT NO. | COVER NO. | INSTALL KOs |
|--------|--------------------|--------------|-----------|-------------|
| NONE | MILBANK LIGHT GRAY | 1160105 | 1160109 | YES |
| -NP | NONE | 1160107 | 1160110 | |
| -NK | MILBANK LIGHT GRAY | 1160106 | 1160109 | NO |
| -NK-NP | NONE | 1160108 | 1160110 | |

NEMA DWG.: #102

| REV. | DATE | DESCRIPTION | BY |
|------|---------|-----------------------------|------|
| E1 | 7/24/12 | CHART VERSIONS (ECO #22677) | D.F. |

| | | | | | |
|--|--|--|--|---|--|
| Material: | | 16 GA. STEEL | |  | |
| Shear/ Die#: | | | | | |
| Finish: | | SEE CHART | | General Offices: Kansas City, MO | |
| Part Wt.: | | | | Title: | SCREW COVER CAN 4 x 6 x 4 TYPE 1 ENCLOSURE |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2" | | Third Angle  | | Catalog No.: | SEE CHART |
| Y F. | | | | Customer: | EALER ELECTRIC |
| Scale: | | NTS | | Drawing No.: | 1011144 |
| Drawn By: | | D.F. | | Date: | 7/24/12 |
| | | Checked By: | | Sheet | 1 of 1 |
| | | Approved By: | | | |






Catalog Number: 464-SC1
Item Description: N1 SCREW COVER ENCL
UPC Code: 784572107045

Brand Name: Milbank
Type: Screw Cover
Special Features: Cover Secured with Plated Screws
Application: Enclosure for Mounting Electrical Equipment
Standard: UL Listed
Number Of Outlet: 0
Material: Steel with Powder Coat Finish
Color: ANSI 61 Gray
Mounting: Wall Mount
NEMA Rating: Type 1



Utility requirements may vary. Always consult the serving utility for their requirements prior to ordering or installing this equipment. This product must always be installed by a licensed electrician. Installation of this equipment may require local electrical inspector approval.

| CATALOG NO. | LABEL NO. |
|----------------|-----------|
| 464-SC1-() | 1002135 |
| RC-464-SC1-() | 1125021 |
| SPSC-644() | 1132714 |



NOTES:



- 1.) BAG ASSY TO BE SHIPPED INSIDE OF ENCLOSURE.

| ITEM | QTY. | PART NUMBER | DESCRIPTION |
|------|------|-------------|--------------------------|
| 1 | 1 | (SEE CHART) | BACK WELDMENT |
| 2 | 1 | (SEE CHART) | COVER PLATE |
| 3 | 2 | 1001290 | SCREW, 10-32 X 5/16 |
| 4 | 1 | (SEE CHART) | LABEL (UL) |
| 5 | 1 | 1002475 | BAG ASSY (GROUND SCREW) |
| 6 | 0.25 | 1002937 | CARTON 4-PER (NOT SHOWN) |

| SUFFIX | FINISH | WELDMENT NO. | COVER NO. | INSTALL KOs |
|--------|--------------------|--------------|-----------|-------------|
| NONE | MILBANK LIGHT GRAY | 1160105 | 1160109 | YES |
| -NP | NONE | 1160107 | 1160110 | |
| -NK | MILBANK LIGHT GRAY | 1160106 | 1160109 | NO |
| -NK-NP | NONE | 1160108 | 1160110 | |

NEMA DWG.: #102

| REV. | DATE | DESCRIPTION | BY |
|------|---------|-----------------------------|------|
| E1 | 7/24/12 | CHART VERSIONS (ECO #22677) | D.F. |

| | | | | | |
|--|--|--|--|---|--|
| Material: | | 16 GA. STEEL | |  | |
| Shear/ Die#: | | | | | |
| Finish: | | SEE CHART | | General Offices: Kansas City, MO | |
| Part Wt.: | | | | Title: | SCREW COVER CAN 4 x 6 x 4 TYPE 1 ENCLOSURE |
| Tolerances: Unless Specified Otherwise X.X ±.1 X.XX ±.03 X.XXX ±.015 X" ±2" | | Third Angle  | | Catalog No.: | SEE CHART |
| Y F. | | | | Customer: | EALER ELECTRIC |
| Scale: | | NTS | | Drawing No.: | 1011144 |
| Drawn By: | | D.F. | | Date: | 7/24/12 |
| | | Checked By: | | Sheet | 1 of 1 |
| | | Approved By: | | | |