



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Alcock St.
79065-0000, TX Pampa
Phone: 806-665-0433
Fax: 806-665-1002



46746 F32T8 TL941/Alto Shatter Resistant *Shat-R-Shield*

Catalog Number	46746
Manufacturer	Shat-R-Shield
Description	Lamp, Shatter-Resistant, Fluorescent, F32T8 TL941/Alto, 32 Watts, 2600 Initial Lumens, 4100 K, 90 Cri, T Shape, 1 In Dia, 48 In Long, T8 Bulb, Medium Bi-Pin (G13) Base, 36000 Avg Life HRS, TL941 Color, Copolymer Coating
Weight per unit	0.5130 (lbs/each)
Product Category	Lighting

Features

average life	36000
Base	Medium Bi-Pin (G13)
lumens	2600
Shape	T
Wattage	32

Material, Color, and Finish

Color	TL941
color rendering index (cri)	90
color temperature	4100

Dimensions and Weight

Diameter	1
Length	48

Descriptions

Description	F32T8 TL941/ALTO SHATTER RESISTANT
extra long description	SHA 46746 F32T8 TL941/ALTO (PK X 30)
Long Description	Lamp, Shatter-Resistant, Fluorescent, F32T8 TL941/ALTO, 32 Watts, 2600 Initial Lumens, 4100 K, 90 CRI, T Shape, 1 IN Dia, 48 IN Long, T8 Bulb, Medium Bi-Pin (G13) Base, 36000 Avg Life Hrs, TL941 Color, Copolymer Coating
Product Type	F32T8 TL941/Alto (PK X 30)
Special Features	Shatter-Resistant Copolymer Coating

Manufacturer Information

Brand	Shat-R-Shield®
GTIN	00726585070084
Manufacturers Part Number	46746
UPC	726585070084



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Alcock St.
79065-0000, TX Pampa
Phone: 806-665-0433
Fax: 806-665-1002

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Straight Linear Fluorescent Lamp

Packaging

Carton	1
Package	30
Weight Per each	0.513

Uses, Certifications, and Standards

Application	Industrial, Food Processing, Food Service, Retail, Hospitality, General Lighting
standard	UL® Listed, NSF Non-Food Zone, NSF Splash Zone, ROHS