



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725



48221025M 25' Magnetic Tape Measure

Milwaukee Electric Tool

MAGNETIC C:

| | |
|------------------|---|
| Catalog Number | 48221025M |
| Manufacturer | Milwaukee Electric Tool |
| Description | The Milwaukee® 25FT Magnetic Tape Measure Delivers A Straighter, Stiffer Blade. The Blade Remains Stiff At 12', Resulting In Less Blade Rollover and Allowing For Efficient Measuring Of Common Jobsite Materials. This Tape Measure Feels Balanced In The Hand For More Control Of The Body and Blade. The Low-Profile Magnet Delivers Improved Top and Bottom Hook Grab. The Blade Retracts Smoothly and Features A Double-Sided Anti-Tear Coating That Reinforces The First 6". The Tape Delivers 15' Of Reach and 12' Of ST |
| Weight per unit | 1.2 (lbs/each) |
| Product Category | Tools & Testers |

Features

| | |
|-------------|-------------|
| Accuracy | +/- 1/16 in |
| Belt Clip | Yes |
| Tape Length | 25 |

Material, Color, and Finish

| | |
|----------------|---------|
| Blade Material | Steel |
| Case Material | PLASTIC |

Dimensions and Weight

| | |
|-------|------|
| Width | 1.18 |
|-------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1811 N. University Suite 100
70507-0000, LA Lafayette
Phone: 337-235-7681
Fax: 337-235-7725

Descriptions

| | |
|------------------------|---|
| Description | 25' MAGNETIC TAPE MEASURE |
| extra long description | MILW 48-22-1025M 25' Magnetic Tape |
| Features | MILWAUKEE® is committed to continuously innovating Layout Hand Tools. With a full line of Tape Measures, MILWAUKEE® provides a solution for every user, ranging from reach, to durability, to compact size. STUD™ is the most durable Tape Measure in the industry with the longest lasting blade, combating blade tear. Wide Blade Tapes deliver the longest reach & straightest standout, allowing just one user to easily and accurately make long distance measurements. In addition to Tape Measures, Milwaukee provides a |
| Long Description | The MILWAUKEE® 25ft Magnetic Tape Measure delivers a Straighter, Stiffer Blade. The blade remains stiff at 12', resulting in less blade rollover and allowing for efficient measuring of common jobsite materials. This tape measure feels balanced in the hand for more control of the body and blade. The low-profile magnet delivers improved top and bottom hook grab. The blade retracts smoothly and features a double-sided anti-tear coating that reinforces the first 6". The tape delivers 15' of Reach and 12' of St |
| Product Type | 25' Magnetic Tape |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Milwaukee® |
| GTIN | 00045242822676 |
| Manufacturers Part Number | 48-22-1025M |
| UPC | 045242822676 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|------------|
| Category Description | HAND TOOLS |
|----------------------|------------|

Packaging

| | |
|-----------------|------|
| Carton | 5 |
| Package | 24 |
| Weight Per each | 1.23 |