

TAPE MEASURES

UP TO **10X LONGER LIFE**



General Information		Tool Specifications			Application Specifications	
Part #	Description	Graduation Type	Magnetic	Tape Color	Hook Type	Blueprint Scale
48-22-5116	16' Magnetic Tape Measure	Inches	YES	Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5117	16' Tape Measure*	Inches		Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5125	25' Magnetic Tape Measure	Inches	YES	Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5126	25' Tape Measure*	Inches		Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5130	30' Magnetic Tape Measure*	Inches	YES	Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5131	30' Tape Measure*	Inches		Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5135	35' Magnetic Tape Measure*	Inches	YES	Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5136	35' Tape Measure*	Inches		Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1'
48-22-5216	5m/16' Magnetic Tape Measure	Inches/Centimeters	YES	Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1' and 1:50, 1:20
48-22-5217	5m/16' Tape Measure*	Inches/Centimeters		Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1' and 1:50, 1:20
48-22-5225	8m/26' Magnetic Tape Measure	Inches/Centimeters	YES	Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1' and 1:50, 1:20
48-22-5226	8m/26' Tape Measure*	Inches/Centimeters		Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1' and 1:50, 1:20
48-22-5233	10m/33' Magnetic Tape Measure*	Inches/Centimeters	YES	Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1' and 1:50, 1:20
48-22-5234	10m/33' Tape Measure*	Inches/Centimeters		Yellow (top) and White (bottom)	360°	1/4": 1', 1/8": 1' and 1:50, 1:20
48-22-5305	5m Magnetic Tape Measure*	Centimeters	YES	Yellow (top) and White (bottom)	360°	1:50, 1:20
48-22-5306	5m Tape Measure*	Centimeters		Yellow (top) and White (bottom)	360°	1:50, 1:20
48-22-5308	8m Magnetic Tape Measure*	Centimeters	YES	Yellow (top) and White (bottom)	360°	1:50, 1:20
48-22-5309	8m Tape Measure*	Centimeters		Yellow (top) and White (bottom)	360°	1:50, 1:20

*Coming Soon