



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155  
75803-8616, TX Palestine  
Phone: 903-723-2141  
Fax: 903-723-1451



## 48892317 5/16" Cobalt Red Helix Drill Bit

*Milwaukee Electric Tool*

Catalog Number	48892317
Manufacturer	Milwaukee Electric Tool
Description	The Milwaukee® Red Helix™ Cobalt 5/16" Drill Bit Are Engineered For Extreme Durability and Longer Life In Hard Metal Applications. The Milwaukee Cobalt Drill Bits Are Designed With A Variable Helix™ That Includes An Aggressive 35° Helix Angle Which Ends At 15°. The Drill Bits Have Quadedge Tip™ to Decrease Heat Buildup and Drill Faster. The 135° Split Point Tip Delivers A Precision Start and Prevents Walking For Fast, Accurate Holes In Hard Metal, PVC and Wood. The Tapered Drill Bits Feature A New Enhanced
Weight per unit	0.0800 (lbs/each)
Product Category	Bits, Parts, Accessories

### Features

Drill Diameter	0.313
Flute Length	3.27
Grade	Heavy Duty
package quantity	1
Shank Diameter	0.3125

### Dimensions and Weight

Length	5.62
--------	------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1620 Highway 155  
75803-8616, TX Palestine  
Phone: 903-723-2141  
Fax: 903-723-1451

## Descriptions

Description	5/16" COBALT RED HELIX DRILL BIT
extra long description	MILW 48-89-2317 5/16 In. COBALT RED
Features	MILWAUKEE® delivers accessories that drive user productivity and cordless efficiency. Solutions are developed with an understanding of jobsite demands, like SHOCKWAVE™ Impact Duty Bits and the fastest cutting, longest life NITRUS™ CARBIDE cutting blades. Milwaukee provides a wide range of accessories covering everything from cutting to fastening with oscillating multi-tool blade, hole saws, SAWZALL® reciprocating saw blades, wood drilling, metal drilling, concrete drilling & chiseling, driving, fastening,
Long Description	The MILWAUKEE® RED HELIX™ Cobalt 5/16" Drill Bit are engineered for extreme durability and longer life in hard metal applications. The Milwaukee Cobalt drill bits are designed with a VARIABLE HELIX™ that includes an aggressive 35° Helix Angle which ends at 15°. The drill bits have QUADEDGE TIP™ to decrease heat buildup and drill faster. The 135° split point tip delivers a precision start and prevents walking for fast, accurate holes in Hard Metal, PVC and wood. The tapered drill bits feature a new ENHANCED
Product Type	5/16 In. Cobalt Red Helix

## Manufacturer Information

Brand	Milwaukee®
GTIN	00045242188321
Manufacturers Part Number	48-89-2317
series	Milwaukee® Cobalt RED HELIX™ Drill Bits
UPC	045242188321

## Taxonomies, Classifications, and Categories

Category Description	BITS, BLADES, AND HOLE SAWS
----------------------	-----------------------------

## Packaging

Carton	1
Package	195
Weight	0.08
Weight Per each	0.08