

Plenum - CMP/CL3P Electronic Wire

Shielded / Cabled

Part#	Description	Rating
75302	22/2 stranded BC	CMP/CL3P
75304	22/4 stranded BC	CMP/CL3P
75306	22/6 stranded BC	CMP/CL3P
75902	18/2 stranded BC	CMP/CL3P
75903	18/3 stranded BC	CMP/CL3P
75904	18/4 stranded BC	CMP/CL3P
75906	18/6 stranded BC	CMP/CL3P
75908	18/8 stranded BC	CMP/CL3P
75702	16/2 stranded BC	CMP/CL3P
75704	16/4 stranded BC	CMP/CL3P

Unshielded / Cabled

Part#	Description	Rating
72302	22/2 stranded BC	CMP/CL3P
72304	22/4 stranded BC	CMP/CL3P
72306	22/6 stranded BC	CMP/CL3P
71902	18/2 stranded BC	CMP/CL3P
71903	18/3 stranded BC	CMP/CL3P
71904	18/4 stranded BC	CMP/CL3P
71906	18/6 stranded BC	CMP/CL3P
71702	16/2 stranded BC	CMP/CL3P
71704	16/4 stranded BC	CMP/CL3P
71502	14/2 stranded BC	CMP/CL3P



Riser - CMR/CL3R Electronic Wire

Shielded / Cabled

Part#	Description	Rating
95211	22/2 stranded BC	CMR/CL3R
67001	22/4 stranded BC	CMR/CL3R
67005	22/6 stranded BC	CMR/CL3R
95214	18/2 stranded BC	CMR/CL3R
95218	18/3 stranded BC	CMR/CL3R
67003	18/4 stranded BC	CMR/CL3R
67006	18/6 stranded BC	CMR/CL3R
95215	16/2 stranded BC	CMR/CL3R
95230	16/4 stranded BC	CMR/CL3R

Unshielded / Cabled

Part#	Description	Rating
51116	22/6 stranded BC	CMR/CL3R
51118	22/8 stranded BC	CMR/CL3R
51122	22/12 stranded BC	CMR/CL3R
51104	18/2 stranded BC	CMR/CL3R
51114	18/4 stranded BC	CMR/CL3R
51117	18/6 stranded BC	CMR/CL3R
51105	16/2 stranded BC	CMR/CL3R
51115	16/4 stranded BC	CMR/CL3R
51140	14/2 stranded BC	CMR/CL3R



Burglar Alarm Wire - CM/CL2

Unshielded / Parallel

Part#	Description	Rating
51101	22/2 stranded BC	CM/CL2
51112	22/4 stranded BC	CM/CL2

Unshielded / Parallel

Part#	Description	Rating
96222	22/2 solid BC	CM/CL2
96238	22/4 solid BC	CM/CL2

Speaker Wire (Oxygen Free*)

Part#	Description	Jacket	Rating
Soundsational™ Round Speaker Cable			
94762	16/2 stranded BC (65/34)	Extruded	CL3
94764	16/4 stranded BC (65/34)	Extruded	CL3
94742	14/2 stranded BC (105/34)	Extruded	CL3
94744	14/4 stranded BC (105/34)	Extruded	CL3
94722	12/2 stranded BC (168/34)	Extruded	CL3
Soundsational™ Parallel Zip Speaker Cable			
94616	16/2 stranded BC (65/34)	Zip	CL2
94614	14/2 stranded BC (105/34)	Zip	CL2
94612	12/2 stranded BC (168/34)	Zip	CL2

Part#	Description	Jacket	Rating
ClearSignal™ Speaker Cable			
94662	16/2 stranded BC (26/30)	Tubed	CL3
94664	16/4 stranded BC (26/30)	Tubed	CL3
94642	14/2 stranded BC (41/30)	Tubed	CL3
94644	14/4 stranded BC (41/30)	Tubed	CL3
Commercial Zip Speaker Cable			
94603	18/2 stranded BC (16/30)	Zip	CL2
94605	16/2 stranded BC (19/.0017)	Zip	CL2
94607	14/2 stranded BC (19/.0017)	Zip	CL2

* Industry standard for "Oxygen Free" is 99.97%