



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## 511140609 18/4 CMR/CL3R Gy 1M'R

*Southwire Company*

Catalog Number	511140609
Manufacturer	Southwire Company
Description	Multi-Conductor Cable, CMR/CL3R (UI), CMG/FT4 (Cul) Type; 1000 FT; 0.166 Inch Outer Diameter; Bare Copper Conductor Material; UI 13, UI 444, Cul Approval
Weight per unit	0.0430 (lbs/ft)
Product Category	Non-Plenum Unshielded Cable

### Features

Conductor Size	18 AWG STRANDED
Number of Conductors	4
Voltage Rating	300 V

### Material, Color, and Finish

Color Code	BLACK, RED, WHITE, GREEN
Conductor Material	Bare Copper
Insulation Material	Polypropylene/Fr Polypropylene
Jacket Color	GRAY
Jacket Material	PVC

### Dimensions and Weight

Length	1000 ft
Outer Diameter	0.166 INCH

### Descriptions

Additional Information	Applicable Standard NEC 725/800; Insulation Thickness 0.006 Inch; Jacket Thickness 0.014 Inch; Packaging Type Reel
Commodity Description	Non-Plenum Unshlded Multicond Cable
Description	18/4 CMR/CL3R GY 1M'R
extra long description	CMR/CL3R (UL), CMG/FT4 (CUL) TYPE; 1000 FT; 0.166 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 13, UL 444, CUL APPROVAL; COMMUNICATION, INTERCOM/P.A SYSTEM, NURSE CALL, POWER LIMITED CIRCUIT, REMOTE CONTROL, SECURITY SYSTEM, SIGNALING, SOUND/AUDIO APPLICATION; 300 V VOLTAGE RATING; -20 TO 60 DEG C TEMPERATURE RATING; 4 CONDUCTOR(S); POLYPROPYLENE/FR POLYPROPYLENE INSULATION MATERIAL; 18 AWG STRANDED CONDUCTOR SIZE; BLACK, RED, WHITE, GREEN COLOR CODE; PVC JACKET MATERIAL; GRAY JACKET COLOR; SIGN
Long Description	MULTI-CONDUCTOR CABLE, CMR/CL3R (UL), CMG/FT4 (CUL) TYPE; 1000 FT; 0.166 INCH OUTER DIAMETER; BARE COPPER CONDUCTOR MATERIAL; UL 13, UL 444, CUL APPROVAL
Product Type	multi-Conductor Cable



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Cables & Cords
Manufacturers Part Number	R40049-1A
Model	51114

## Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC CABLE
Type	CMR/CL3R (UL), CMG/FT4 (CUL)

## Availability

minimum qty	1000
-------------	------

## Packaging

Carton	1000
Weight Per foot	0.043

## Uses, Certifications, and Standards

Application	Communication, Intercom/P.A System, Nurse Call, Power Limited Circuit, Remote Control, Security System, Signaling, Sound/Audio
Approval	UL 13, UL 444, CUL
Temperature Rating	-20 TO 60 DEG C