



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



52C20 4SQ, 2G, 1/4" RSD DVC RNG

Abb Installation Products, Inc

| | |
|------------------|--|
| Catalog Number | 52C20 |
| Manufacturer | Abb Installation Products, Inc |
| Description | Two Gang Square Device Cover, 2.3 Cubic Inches, 4 Inch Square X 1/4 Inch Raised, Pre-Galvanized Steel, For Use With Dry Wall |
| Weight per unit | 0.1300 (lbs/each) |
| Product Category | Bar Hangers & Outlet Box Accy. |

Features

| | |
|------------------|--------|
| Knockouts | 0 |
| Material | Steel |
| number of outlet | 2 |
| Shape | Square |

Material, Color, and Finish

| | |
|--------|----------------|
| Color | Silver |
| Finish | Pre-Galvanized |

Dimensions and Weight

| | |
|------|----------|
| Size | 4 Inches |
|------|----------|

Descriptions

| | |
|------------------------|--|
| Description | 4SQ, 2G, 1/4" RSD DVC RNG |
| extra long description | ABB 52C20-25 4SQ RNG 2G, 1/4IN RSD, |
| Long Description | Two Gang Square Device Cover, 2.3 Cubic Inches, 4 Inch Square x 1/4 Inch Raised, Pre-Galvanized Steel, For use with Dry Wall |
| Product Type | 4SQ RNG 2G, 1/4IN RSD, 2.3cu |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Steel City |
| GTIN | 00785991139105 |
| Manufacturers Part Number | 52C20-25 |
| UPC | 785991139105 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------|
| Category Description | 4 SQ BOXES |
| Type | Outlet Box Covers |

Availability

| | |
|--------|----------|
| Status | Inactive |
|--------|----------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.13 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|----------------------|
| Application | For use with drywall |
| standard | UL E2969 / UL E2969 |