



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 5851W 20A 250V Spec SNGL Rec *Pass & Seymour/Legrand*

Catalog Number	5851W
Manufacturer	Pass & Seymour/Legrand
Description	Single Receptacle, 20 A, 250 V Ac, 2 Poles, 3 Wires, Back Wire Connection, Wall Mount, 1.380 In Length, 1.08 In Width, 3.28 In Height, Thermoplastic, White, Corrosion Resistant, 3.3000 LB
Weight per unit	0.1604 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

amperage rating	20 A
connection	Wire Ground
Poles	2 in
Wire Size	4 in

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	20A 250V SPEC SNGL REC
-------------	------------------------

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007585124
sub brand	Pass & Seymour
UPC	785007585124

### Taxonomies, Classifications, and Categories

Category Description	Industrial recepticals
Type	Straight Blade Receptacle

### Packaging

Carton	10
Package	100
Weight Per each	0.1604

### Uses, Certifications, and Standards

Mounting	WALL
standard	UL 498



## HEAVY-DUTY SPEC GRADE SINGLE RECEPTACLES, SIDE WIRE, 20A, 250V, WHITE

5851W | [Pass & Seymour](#)

### FEATURES & BENEFITS

Heavy-Duty Spec Grade Single Receptacle, Side Wire 20amp 250volt, White

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wire power contacts for lasting retention.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Type: Single Receptacles  
Duty: Heavy Duty  
Special Features: Side Wire

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: C22.2 No.42  
CSA Standard: Yes  
cURus: No  
Federal Spec: No  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406  
UR: No

#### DIMENSIONS

Depth (US): 1.08"  
Height (US): 3.28"  
Width (US): 1.380"

## TECHNICAL INFORMATION

Amps: 20A

Volts: 250V

Volts (AC): 250

Capacity: Single

Grade Type: Federal Specification

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

