



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **600T2 600 Al/Cu 2 Cond, 2 Hole Stacked Lug**

*Nsi Industries*

Catalog Number	600T2
Manufacturer	Nsi Industries
Description	2 Port Stacked Lug 600 MCM - 2 Awg Stacked Lugs Are Large Size Set Screw Connectors With Wire Holes Stacked On Top Of Each Other to Minimize The Width Of The Connector. Made Of 6061T-6 Aluminum Alloy. Tin Plated For Low Contact Resistance. Suitable For Use With Both Copper and Aluminum Conductors. Rated 600 Volts (2000V Max. Per UL486B). UL486A/B Listed. Temperature Rating 90 Degrees C. Mounting Hole Spacing Is Nema Standard Of 1.75".
Weight per unit	0.9000 (lbs/each)
Product Category	Large Terminals & Connectors

### **Features**

Material	Aluminum
Poles	1
Voltage Rating	600
Warranty	1 YEAR

### **Material, Color, and Finish**

Color	Silver
Finish	Aluminum



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	600 AL/CU 2 COND, 2 HOLE STACKED LUG
extra long description	NSI 600T-2 STEP PANEL LUG (4) 600-2
Features	2 Port Stacked Lug 600 MCM - 2 AWG Stacked Lugs are large size set screw connectors with wire holes stacked on top of each other to minimize the width of the connector. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600 volts (2000V max. per UL486B). UL486A/B Listed. Temperature rating 90 degrees C. Mounting hole spacing is NEMA standard of 1.75".
Long Description	2 Port Stacked Lug 600 MCM - 2 AWG Stacked Lugs are large size set screw connectors with wire holes stacked on top of each other to minimize the width of the connector. Made of 6061T-6 aluminum alloy. Tin plated for low contact resistance. Suitable for use with both copper and aluminum conductors. Rated 600 volts (2000V max. per UL486B). UL486A/B Listed. Temperature rating 90 degrees C. Mounting hole spacing is NEMA standard of 1.75".
Product Type	Step Panel Lug (4) 600-2 (Pack Of 24)

## Manufacturer Information

Brand	NSi
GTIN	00662381001825
Manufacturers Part Number	600T-2
sub brand	Mechanical Connector
UPC	662381001825

## Taxonomies, Classifications, and Categories

Category Description	SPLIT BOLTS
----------------------	-------------

## Packaging

Carton	1
Package	2
Weight Per each	0.9

## Uses, Certifications, and Standards

environmental conditions	90 C
Temperature Rating	90 C