



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



61521 3-Phase/Motor Rotation Tester

Ideal

| | |
|------------------|---|
| Catalog Number | 61521 |
| Manufacturer | Ideal |
| Description | 3-Phase/Motor Rotation Tester, Voltage Rating: 100 - 600 Vac (10 - 400 HZ) Nominal For Phase Presence Indication, Amperage Rating: 18 Milamp Maximum Consumption, 3 PH Phase, Temperature Rating: 5 - 131 Deg F Operating, -4 to 158 Deg F Storage, Display: Neon Lamps and Leds, Dimensions: 6 In Height X 2.8 In Width X 1.4 In Depth, Phase Rotary Field Direction: 1 - 600 Vac (2 - 400 HZ), Determination Of Motor Rotation: 1 - 600 Vac (2 - 400 HZ) Requires Greater Than 1/2 Turn, Over Load Protection: 550 V (Between |
| Weight per unit | 1.1 (lbs/each) |
| Product Category | Testers & Accessories |

Features

| | |
|-----------------|---|
| amperage rating | 18 MILAMP Maximum Consumption |
| dimensions | 6 IN Height X 2.8 IN Width X 1.4 IN Depth |
| display | Neon Lamps And LEDs |
| Phase | 3 Ph |
| Voltage Rating | 100 - 600 VAC (10 - 400 HZ) Nominal For Phase Presence Indication |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Description | 3-PHASE/MOTOR ROTATION TESTER |
| extra long description | IDEAL 61-521 3 PHASE MOTOR ROTATION |
| Features | Identifies three-phase sequencesIndicates motor rotationChecks for open phasesFor use up to 600V2-year warranty |
| Long Description | 3-Phase/Motor Rotation Tester, Voltage Rating: 100 - 600 VAC (10 - 400 HZ) Nominal For Phase Presence Indication, Amperage Rating: 18 MILAMP Maximum Consumption, 3 Ph Phase, Temperature Rating: 5 - 131 DEG F Operating, -4 To 158 DEG F Storage, Display: Neon Lamps And LEDs, Dimensions: 6 IN Height X 2.8 IN Width X 1.4 IN Depth, Phase Rotary Field Direction: 1 - 600 VAC (2 - 400 HZ), Determination Of Motor Rotation: 1 - 600 VAC (2 - 400 HZ) Requires Greater Than 1/2 Turn, Over Load Protection: 550 V (Between |
| Product Type | 3 Phase Motor Rotation Tester |
| Special Features | Identifies three-phase sequence; Indicates motor rotation; Checks for open phases; For use up to 600 V; Meets IEC-1010 (EN61010) safety requirements; 2-year warranty; Includes carrying case |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Ideal |
| GTIN | 00783250615216 |
| Manufacturers Part Number | 61-521 |
| sub brand | Ideal |
| UPC | 783250615216 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | TEST EQUIPMENT, TESTERS AND MULTIMETERS |
| Type | 3-Phase/Motor Rotation Tester |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 1.05 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| standard | Meets IEC-1010 (EN61010) Safety Requirements, CE N12966, CAT III 600V |
| Temperature Rating | 5 - 131 DEG F Operating, -4 To 158 DEG F Storage |