ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

61603 DIGITAL MULTIMETER

IDEAL

Catalog Number	61603
Manufacturer	IDEAL
Description	DIGITAL MULTIMETER
Weight per unit	0.9000 (lbs/each)
Product Category	Test Equipment - Multimeters

Features

AC Voltage Range	200.0/300 V
Accuracy	1.2 PERCENT AC VOLTAGE, 0.5 PERCENT DC VOLTAGE, 1.5 PERCENT DC CURRENT, 1 PERCENT RESISTANCE, 2.5 PERCENT TEMPERATURE
Battery Type	9 V
DC Current Range	200.0 MILLIAMPERE, 10.00 AMPERE
DC Voltage Range	200.0 MILLIVOLT, 2.000/20.00/200.0/300 V
Inclusion	TEST LEADS, THERMOCOUPLE
Parameter Measured	AC/DC VOLTAGE, AC/DC CURRENT, AUDIBLE CONTINUITY, BATTERY TEST, DIODE TEST, RESISTANCE, TEMPERATURE
Resistance Range	200.0/2.000/20.00/200.0 KILO OHM, 20.00 MEGA OHM
Temperature Range	-4 TO 1382 DEG F

Descriptions

Commodity Description	MULTIMETERS
Description	DIGITAL MULTIMETER
Long Description	DIGITAL MULTIMETER MULTIMETER, DIGITAL; PARAMETER MEASURED AC/DC VOLTAGE, AC/DC CURRENT, AUDIBLE CONTINUITY, BATTERY TEST, DIODE TEST, RESISTANCE, TEMPERATURE; AC VOLTAGE RANGE 200.0/300 V; DC VOLTAGE RANGE 200.0 MILLIVOLT, 2.000/20.00/200.0/300 V
Product Type	Multimeter
Extra Long Description	DIGITAL TYPE; 1.2 PERCENT AC VOLTAGE, 0.5 PERCENT DC VOLTAGE, 1.5 PERCENT DC CURRENT, 1 PERCENT RESISTANCE, 2.5 PERCENT TEMPERATURE ACCURACY; UL 61010, UL (CANADA AND US), CE APPROVAL; 9 V BATTERY TYPE; TEST LEADS, THERMOCOUPLE INCLUSION; -4 TO 1382 DEG F TEMPERATURE RANGE; AC/DC VOLTAGE, AC/DC CURRENT, AUDIBLE CONTINUITY, BATTERY TEST, DIODE TEST, RESISTANCE, TEMPERATURE PARAMETER MEASURED; 200.0/2.000/20.00/200.0 KILO OHM, 20.00 MEGA OHM RESISTANCE RANGE; 200.0 MILLIAMPERE, 10.00 AMPERE DC CURRENT RANGE;

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
Nacogdoches, TX 75964-0
Phone: 9365697941
Fax: 9365604685

Manufacturer Information

Brand	Ideal
	Resi-Pro[T]
GTIN	00783250613106
Manufacturers Part Number	61-310
UPC	783250

Taxonomies, Classifications, and Categories

Category Description	TEST EQUIPMENT, TESTERS AND MULTIMETERS
Type	DIGITAL

Packaging

Carton	1
Weight Per Each	0.9000 (lbs/each)

Uses, Certifications, and Standards

Approval	UL 61010, UL (CANADA AND US), CE