



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 621803 7" 13W Led Disk Light 27K/3K/35K/4K/5K Bronze 120V *Satco*

Catalog Number	621803
Manufacturer	Satco
Description	7-Inch Led Disk Light - 5-CCT Selectable 27K/3K/35K/4K/5K - Bronze Finish
Weight per unit	0.5800 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.125
Lamp Included	Integrated
Lamp Type	LED
Material	Steel
Number of Lamps	1
Reflector Type	White
Socket Type	Integrated
Voltage Rating	120
Wattage	15

### Material, Color, and Finish

Finish	Bronze
fixture material	steel
Style	CONTEMPORARY

### Dimensions and Weight

Height	1.42
Length	7.42
Width	7.42



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	7" 13W LED DISK LIGHT 27K/3K/35K/4K/5K BRONZE 120V
extra long description	SATCO 62/1803 7" LED DISK LIGHT BRO
Long Description	7-Inch LED Disk Light - 5-CCT Selectable 27K/3K/35K/4K/5K - Bronze Finish
Product Type	7" Led Disk Light Bronze Finis
Special Features	Warranty: 5 Year Limited - Fixtures ; Lumens: 780-910 ; CCT: 2700K/3000K/3500K/4000K/5000K ; Color Temperature: Warm to Cool White ; CRI: 93 ; Lamp Base: Integrated LED ; Hours Rated: 50000 ; DLC Approved: No ; Energy Star: Yes ; Location Rating: Wet ; Dimension String: H:1.42" DIA:7.42" ; CEC: California T24 Listed ; Closet Rated: No ; FCC Compliant: Yes ; JA8 Compliant: Yes ; Amps: 0.125A ; Efficacy: 52.00/56.33/60.67 lm/w ; Incandescent Equivalent: 60W ; Operating Frequency: 60Hz ; Surge Protection: Bui

## Manufacturer Information

Brand	Nuvo
GTIN	00045923625886
Manufacturers Part Number	62/1803
UPC	045923625886

## Taxonomies, Classifications, and Categories

Category Description	Led Lighting
Type	LED Decorative

## Packaging

Carton	1
Weight Per each	0.58

## Uses, Certifications, and Standards

Application	Close-to-Ceiling
Frequency Rating	60
Mounting	CEILING
standard	cETLus - Listed