



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



621264R1 7" Led Disc Light Hi Lumen WH 4K

Satco

Catalog Number	621264R1
Manufacturer	Satco
Description	7 In. Led Flush Mount Fixture Disk Light - White Finish 4000K 90 Cri
Weight per unit	0.5500 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	Connector
Fixture Type	Flush Mount
lumens	1500
Material	Aluminum
Voltage	120
Warranty	5 Year Limited - Fixtures
Wattage	15

Descriptions

Description	7" LED DISC LIGHT HI LUMEN WH 4K
extra long description	SATCO 62-1264R1 7 IN LED DISC LIGHT
Long Description	7 in. LED Flush Mount Fixture Disk Light - White Finish 4000K 90 CRI
Product Type	7 In Led Disc Light - High Lumen WHT 40K
Special Features	Lawful for sale in California ; Finish: White ; Voltage: 120 ; Suitable for Closet Installations ; Energy Star: Yes ; IC Rated: No ; Incandescent Equivalent: 75W ; Fixture Material: Aluminum ; Lens Material: Acrylic ; Operating Temperature: -17C (+1.4F) to a maximum of +46C (+114.8F) ; Rated for Vapor Tight: No ; Country of Origin: China ; Color Temperature: Cool White ; CCT: 4000K ; CRI: 90 ; Dimmable: Yes - Dimmable ; Average Rated Hours: 50000

Manufacturer Information

Brand	Nuvo
GTIN	00045923621444
Manufacturers Part Number	62-1264R1
sub brand	Nuvo
UPC	045923621444

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	LED Disc Light



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight	0.51
Weight Per each	0.55

Uses, Certifications, and Standards

environmental conditions	Indoor - Wet
Mounting	CEILING
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
standard	cETLus