



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104



6314043 480V, 3P + G, 5HP Rating Receptacle, Female *Meltric Corporation*

Catalog Number	6314043
Manufacturer	Meltric Corporation
Description	Meltric; Receptacle; Decontactor; DSN20, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 14 Awg, Max 12 Awg; Amperage Rating: 20 Amp; Voltage Rating: 480 Vac; Phase: 3; Color: Blue; Nema Rating: 4X; Connection: Female; Temperature Rat
Weight per unit	0.4600 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	20 CI
connection	Female
Material	Polyster
Phase	3 in
Poles	3 in
Voltage Rating	Overall Dimension 4-1/16 Inch Width x 3-3/16 Inch Depth x 4-3/4 Inch Height; Fuel Type Natural; Capacity 23000 to 290000 BTU/Hour; Pressure Tapping 1/8 Inch Threaded with Plug; Pressure Regulator Set Point 3.5 Inch WC
Wire Size	Min 14 AWG, Max 12 AWG

Material, Color, and Finish

Color	Blue Light
-------	------------

Descriptions

Description	480V, 3P + G, 5HP RATING RECEPTACLE, FEMALE
extra long description	MEL 63-14043 DSN20 RECEPTACLE
Long Description	Meltric; Receptacle; Decontactor; DSN20, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 14 AWG, Max 12 AWG; Amperage Rating: 20 AMP; Voltage Rating: 480 VAC; Phase: 3; Color: Blue; Nema Rating: 4X; Connection: Female; Temperature Rat
Product Type	DSN20 Receptacle
Special Features	Features: Switch Ratings (AC Only): Branch Circuit & Motor Circuit Disconnect Switching; Short Circuit Rating: 100 KILO AMP Close & Withstand Testing Was Performed With RK1 Current Limiting Fuses Sized At 400 PEC Of The Highest Full Load Motor Ampacity Associated With The Devices HP Rating; Horsepower Ratings: 5 HP AT 3 PH, 480 V; Polarity: 3P+G



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104

Manufacturer Information

Brand	Meltric
GTIN	00784474544610
Manufacturers Part Number	63-14043
sub brand	Decontactor
UPC	784474544610

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	DSN20, Switch Rated

Packaging

Carton	1
Weight Per each	0.46

Uses, Certifications, and Standards

nema rating	78101111376
standard	UL, CSA, IEC, CE (Contact Customer Service)
Temperature Rating	-40 to 140 F