



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253



6334043 480V, 3P + G, 10HP Rating Receptacle, Female *Meltric Corporation*

Catalog Number	6334043
Manufacturer	Meltric Corporation
Description	Meltric; Receptacle; Decontactor; DSN30, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 14 Awg, Max 8 Awg; Auxiliary Contacts - Max 14 Awg; Amperage Rating: 30 Amp; Voltage Rating: 480 Vac; Phase: 3; Color: Blue; Nema Rating: 4X; Con
Weight per unit	0.7100 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	30 W
connection	Female
Material	Polyster
Phase	3 in
Poles	3 in
Voltage Rating	Overall Dimension 4-1/16 Inch Width x 3-3/16 Inch Depth x 4-3/4 Inch Height; Fuel Type Natural; Capacity 23000 to 290000 BTU/Hour; Pressure Tapping 1/8 Inch Threaded with Plug; Pressure Regulator Set Point 3.5 Inch WC
Wire Size	Min 14 AWG, Max 8 AWG; Auxilliary Contacts - Max 14 AWG

Material, Color, and Finish

Color	Blue Light
-------	------------

Descriptions

Description	480V, 3P + G, 10HP RATING RECEPTACLE, FEMALE
extra long description	MEL 63-34043 DSN30 RECEPTACLE
Long Description	Meltric; Receptacle; Decontactor; DSN30, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 14 AWG, Max 8 AWG; Auxiliary Contacts - Max 14 AWG; Amperage Rating: 30 AMP; Voltage Rating: 480 VAC; Phase: 3; Color: Blue; Nema Rating: 4X; Con
Product Type	DSN30 Receptacle
Special Features	Features: Switch Ratings (AC Only): Branch Circuit & Motor Circuit Disconnect Switching; Short Circuit Rating: 100 KILO AMP Close & Withstand Testing Was Performed With RK1 Current Limiting Fuses Sized At 400 PEC Of The Highest Full Load Motor Ampacity Associated With The Devices HP Rating; Horsepower Ratings: 10 HP AT 3 PH, 480 V; Polarity: 3P+G



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253

Manufacturer Information

Brand	Meltric
GTIN	00784474544207
Manufacturers Part Number	63-34043
sub brand	Decontactor
UPC	784474544207

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	DSN30, Switch Rated

Packaging

Carton	1
Weight Per each	0.71

Uses, Certifications, and Standards

nema rating	78101111376
standard	UL, CSA, IEC, CE (Contact Customer Service)
Temperature Rating	-40 to 140 F