



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6334043 480V, 3P + G, 10HP Rating Receptacle, Female

Meltric Corporation

| | |
|------------------|---|
| Catalog Number | 6334043 |
| Manufacturer | Meltric Corporation |
| Description | Meltric; Receptacle; Decontactor; DSN30, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 14 Awg, Max 8 Awg; Auxiliary Contacts - Max 14 Awg; Amperage Rating: 30 Amp; Voltage Rating: 480 Vac; Phase: 3; Color: Blue; Nema Rating: 4X; Con |
| Weight per unit | 0.7100 (lbs/each) |
| Product Category | Pin & Sleeve Devices |

Features

| | |
|-----------------|---|
| amperage rating | 30 W |
| connection | Female |
| Material | Polyster |
| Phase | 3 in |
| Poles | 3 in |
| Voltage Rating | Overall Dimension 4-1/16 Inch Width x 3-3/16 Inch Depth x 4-3/4 Inch Height; Fuel Type Natural; Capacity 23000 to 290000 BTU/Hour; Pressure Tapping 1/8 Inch Threaded with Plug; Pressure Regulator Set Point 3.5 Inch WC |
| Wire Size | Min 14 AWG, Max 8 AWG; Auxilliary Contacts - Max 14 AWG |

Material, Color, and Finish

| | |
|-------|------------|
| Color | Blue Light |
|-------|------------|

Descriptions

| | |
|------------------|--|
| Description | 480V, 3P + G, 10HP RATING RECEPTACLE, FEMALE |
| Long Description | Meltric; Receptacle; Decontactor; DSN30, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 14 AWG, Max 8 AWG; Auxiliary Contacts - Max 14 AWG; Amperage Rating: 30 AMP; Voltage Rating: 480 VAC; Phase: 3; Color: Blue; Nema Rating: 4X; Con |
| Product Type | DSN30 Receptacle |
| Special Features | Features: Switch Ratings (AC Only): Branch Circuit & Motor Circuit Disconnect Switching; Short Circuit Rating: 100 KILO AMP Close & Withstand Testing Was Performed With RK1 Current Limiting Fuses Sized At 400 PEC Of The Highest Full Load Motor Ampacity Associated With The Devices HP Rating; Horsepower Ratings: 10 HP AT 3 PH, 480 V; Polarity: 3P+G |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Meltric |
| GTIN | 00784474544207 |
| Manufacturers Part Number | 63-34043 |
| sub brand | Decontactor |
| UPC | 784474544207 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Residential GFCI devices |
| Type | DSN30, Switch Rated |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 0.71 |

Uses, Certifications, and Standards

| | |
|--------------------|---|
| nema rating | 78101111376 |
| standard | UL, CSA, IEC, CE (Contact Customer Service) |
| Temperature Rating | -40 to 140 F |