



Southwire™

TOOLS & EQUIPMENT

QWIKtape™ & QWIKline™

QWIKtape™

**THREAD/MEASURE CONDUIT AND
PULL WIRE WITH ONE PRODUCT**

**PRINTED WITH ACCURATE,
SEQUENTIAL, EASY-TO-READ
FOOTAGE MARKINGS**

**LOW COEFFICIENT OF FRICTION
MINIMIZES DUCT MELTING**

EASILY BLOWN THROUGH CONDUIT

QWIKline™

**READY TO USE STORAGE CONTAINER
QUICKLY DISPENSES A TANGLE
FREE LINE**

**USED TO PULL ELECTRICAL AND
COMMUNICATION WIRE**

RESISTANT TO ROT AND MILDEW

MADE IN AMERICA



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



QWIKtape™ & QWIKline™

Model #	Stock #	Description	Pallet Quantity	Length (ft.)	Width (in.)	Tensile Strength (lbs.)
SWCMT160-3000S	64584901	Conduit Measuring Tape 160-LB x 3000-FT Spool	144	3000	3/16	160
SWMT400-4500P	64585001	QWIKtape™ 400-LB x 4500-FT Bucket	36	4500	3/16	400
SWMT1250-3000S	64585101	QWIKtape™ 1250-LB x 3000-FT Spool	36	3000	1/2	1250
SWQT1250-500S	65128740	QWIKtape™ 1250-LB x 500-FT Spool	128	500	1/2	1250
SWQT1250-1000S	65128840	QWIKtape™ 1250-LB x 1000-FT Spool	128	1000	1/2	1250
SWQT1250-1500S	65128940	QWIKtape™ 1250-LB x 1500-FT Spool	96	1500	1/2	1250
SWQT1250-5000S	65129040	QWIKtape™ 1250-LB x 5000-FT Spool	18	5000	1/2	1250
SWDQT1250-3000S	65129140	QWIKtape™ 1250-LB x 3000-FT Spool - DETECTABLE	36	3000	1/2	1250
SWMT1800-3000S	64585201	QWIKtape™ 1800-LB x 3000-FT Spool	36	3000	5/8	1800
SWQT1800-500S	65129240	QWIKtape™ 1800-LB x 500-FT Spool	128	500	5/8	1800
SWQT1800-1000S	65129340	QWIKtape™ 1800-LB x 1000-FT Spool	128	1000	5/8	1800
SWQT1800-1500S	65129440	QWIKtape™ 1800-LB x 1500-FT Spool	96	1500	5/8	1800
SWQT1800-5000S	65129540	QWIKtape™ 1800-LB x 5000-FT Spool	12	5000	5/8	1800
SWDQT1800-3000S	65129640	QWIKtape™ 1800-LB x 3000-FT Spool - DETECTABLE	36	3000	5/8	1800
SWMT2500-3000S	64585401	QWIKtape™ 2500-LB x 3000-FT Spool	36	3000	3/4	2500
SWQT2500-500S	65129740	QWIKtape™ 2500-LB x 500-FT Spool	96	500	3/4	2500
SWQT2500-1000S	65129840	QWIKtape™ 2500-LB x 1000-FT Spool	96	1000	3/4	2500
SWQT2500-1500S	65130040	QWIKtape™ 2500-LB x 1500-FT Spool	64	1500	3/4	2500
SWQT2500-5000S	65130140	QWIKtape™ 2500-LB x 5000-FT Spool	12	5000	3/4	2500
SWDQT2500-3000S	65130340	QWIKtape™ 2500-LB x 3000-FT Spool - DETECTABLE	36	3000	3/4	2500
PL6500	58280540	QWIKline™ 210-LB x 6500-FT Bucket	36	6500	N/A	210
PL500	58280640	QWIKline™ 210-LB x 500-FT Canister	N/A	500	N/A	210
PL2200	65130440	QWIKline™ 500-LB x 2200-FT Bucket	36	2200	N/A	500