



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



6364043 480V, 3P + G, 20HP Rating Receptacle, Female *Meltric Corporation*

Catalog Number	6364043
Manufacturer	Meltric Corporation
Description	Meltric; Receptacle; Decontactor; DSN60, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 12 Awg, Max 4 Awg; Auxiliary Contacts - Max 14 Awg; Amperage Rating: 60 Amp; Voltage Rating: 480 Vac; Phase: 3; Color: Blue; Nema Rating: 4X; Con
Weight per unit	0.9400 (lbs/each)
Product Category	Pin & Sleeve Devices

Features

amperage rating	60 Hz
connection	Female
Material	Polyster
Phase	3 in
Poles	3 in
Voltage Rating	Overall Dimension 4-1/16 Inch Width x 3-3/16 Inch Depth x 4-3/4 Inch Height; Fuel Type Natural; Capacity 23000 to 290000 BTU/Hour; Pressure Tapping 1/8 Inch Threaded with Plug; Pressure Regulator Set Point 3.5 Inch WC
Wire Size	Min 12 AWG, Max 4 AWG; Auxilliary Contacts - Max 14 AWG

Material, Color, and Finish

Color	Blue Light
-------	------------

Descriptions

Description	480V, 3P + G, 20HP RATING RECEPTACLE, FEMALE
Long Description	Meltric; Receptacle; Decontactor; DSN60, Switch Rated; Material: Polyster; Number Of Poles: 3; Wire Size: Min 12 AWG, Max 4 AWG; Auxiliary Contacts - Max 14 AWG; Amperage Rating: 60 AMP; Voltage Rating: 480 VAC; Phase: 3; Color: Blue; Nema Rating: 4X; Con
Product Type	DSN60 Receptacle
Special Features	Features: Switch Ratings (AC Only): Branch Circuit & Motor Circuit Disconnect Switching; Short Circuit Rating: 100 KILO AMP Close & Withstand Testing Was Performed With RK1 Current Limiting Fuses Sized At 400 PEC Of The Highest Full Load Motor Ampacity Associated With The Devices HP Rating; Horsepower Ratings: 20 HP AT 3 PH, 480 V; Polarity: 3P+G



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Meltric
GTIN	00784474545433
Manufacturers Part Number	63-64043
sub brand	Decontactor
UPC	784474545433

Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	DSN60, Switch Rated

Packaging

Carton	1
Weight Per each	0.94

Uses, Certifications, and Standards

nema rating	78101111376
standard	UL, CSA, IEC, CE (Contact Customer Service)
Temperature Rating	-40 to 140 F