



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



646516M 5/16" Magnetic Nut Driver Cushion-Grip

Klein Tools

Catalog Number	646516M
Manufacturer	Klein Tools
Description	
Weight per unit	0.2200 (lbs/each)
Product Category	Pliers, Wrenches, Saw, Pouches

Features

Shank Length	6"
--------------	----

Dimensions and Weight

Overall Length	9-3/4"
----------------	--------

Descriptions

Description	5/16" MAGNETIC NUT DRIVER CUSHION-GRIP
Product Type	5/16" Magnetic Nut Driver
Special Features	Exclusive hollow shaft design with Rare Earth magnetic tip features unobstructed pass-through, even on long bolts.

Manufacturer Information

Brand	KLEIN TOOLS
GTIN	00092644651403
Manufacturers Part Number	646-5/16M
UPC	092644651403

Taxonomies, Classifications, and Categories

Category Description	HAND TOOLS
Type	Magnetic Tip Hollow-Shaft Nut Drivers - 6" Shafts

Packaging

Carton	1
Package	6
Weight Per each	0.22

MAGNETIC TIP NUT DRIVERS

Hollow Shaft



**KLEIN
TOOLS®**

Magnetic Tip Nut Drivers – Hollow Shaft

KLEIN TOOLS
For Professionals... Since 1857®

Rare Earth Magnetic Tip and Hollow Shaft Design... Performance For Professionals

Introducing new cushion-grip nut drivers from Klein Tools that combine the power of rare earth magnetic tips and the convenience of a hollow shaft design. Available in 1/4" and 5/16" hex sizes and a variety of shaft lengths (from a 1-1/2" stubby to an 18" super long), Klein's rare earth magnetic tip nut drivers securely hold fasteners in place for one-handed operation and easily drive nuts on long bolt applications, as well as many electrical and HVAC/R panels.


Features

Patent pending hollow shaft design with Rare Earth magnetic tip.



Color-coded handle end quickly identifies nut driver size.

Hex sizes available in both 1/4" and 5/16".



Hollow shaft facilitates work on bolt applications.

Chrome-plated shaft helps prevent corrosion.

Meets or exceeds applicable ASME/ANSI specifications.

Internal flanges provide solid, twist-resistant shaft anchor.

Cushion-grip handle for greater torque and comfort.

⚠ WARNINGS:

- Always wear approved eye protection.
- NOT insulated. Will NOT protect against electrical shock.

Ordering Information

	Cat. No.	UPC No. 0-92644+	Description	Handle End Color	Shaft Length	Overall Length
NEW!	610-1/4M	65135-9	1/4" Magnetic Tip Nut Driver – Hollow Shaft	Red	1-1/2" (38 mm)	3-1/2" (89 mm)
NEW!	610-5/16M	65136-6	5/16" Magnetic Tip Nut Driver – Hollow Shaft	Yellow	1-1/2" (38 mm)	3-1/2" (89 mm)
NEW!	610M	65143-4	2-Piece Magnetic Tip Nut Driver Set	Red and Yellow	1-1/2" (38 mm)	3-1/2" (89 mm)
NEW!	630-1/4M	65137-3	1/4" Magnetic Tip Nut Driver – Hollow Shaft	Red	3" (76 mm)	6-3/4" (171 mm)
NEW!	630-5/16M	65138-0	5/16" Magnetic Tip Nut Driver – Hollow Shaft	Yellow	3" (76 mm)	6-3/4" (171 mm)
NEW!	630M	65144-1	2-Piece Magnetic Tip Nut Driver Set	Red and Yellow	3" (76 mm)	6-3/4" (171 mm)
NEW!	646-1/4M	65139-7	1/4" Magnetic Tip Nut Driver – Hollow Shaft	Red	6" (152 mm)	9-3/4" (248 mm)
NEW!	646-5/16M	65140-3	5/16" Magnetic Tip Nut Driver – Hollow Shaft	Yellow	6" (152 mm)	9-3/4" (248 mm)
NEW!	646M	65145-8	2-Piece Magnetic Tip Nut Driver Set	Red and Yellow	6" (152 mm)	9-3/4" (248 mm)
NEW!	618-1/4M	65141-0	1/4" Magnetic Tip Nut Driver – Hollow Shaft	Red	18" (457 mm)	21-3/4" (552 mm)
NEW!	618-5/16M	65142-7	5/16" Magnetic Tip Nut Driver – Hollow Shaft	Yellow	18" (457 mm)	21-3/4" (552 mm)



KLEIN TOOLS

For Professionals... Since 1857®

Chicago, IL 60659-9033
www.kleintools.com