ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



651413 Led Double Head Security Light W/MS 3K/4K/5K BRZ

Satco

Catalog Number	651413
Manufacturer	Satco
Description	20 Watt Led Dual Head Security Flood Light - 9.61 X 7.32 X 7.17 - 80 Cri - 3000K/4000K/5000K CCT - Bronze Finish - Wet Location Rated
Weight per unit	2.8 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.180 to 0.080
Lamp Type	LED
Power Rating	>0.7
Reflector Type	Clear
Socket Type	Integrated
Voltage Rating	120 to 277

Material, Color, and Finish

fixture material	die-cast aluminum
Style	Utility

Dimensions and Weight

Size	W:9.61 H:7.17 E:7.32

Descriptions

Description	LED DBL HEAD SECURITY LIGHT W/SNSR 3K/4K/5K BRZ
extra long description	SAT 65/1413 LED 2 BULLET HEAD SECUR
Long Description	20 Watt LED Dual Head Security Flood Light - 9.61 x 7.32 x 7.17 - 80 CRI - 3000K/4000K/5000K CCT - Bronze Finish - Wet Location Rated
Product Type	Led 2 Bullet Head Security LGT
Special Features	Warranty: 5-Years ; FCC Compliant: True ; Photo Cell: Built-in Photocell ; Cct Selectable: True ; CCT (Kelvin Temp): 3000K/4000K/5000K ; Hours Rated: 50000 ; Beam Angle (degree): 110 ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Clear ; Lens Material: Polycarbonate (PC) ; Operating Temp: -40F to +122F (-40C to +50C) ; Watts: 20W ; Lumens: 2600L/2700L/2900L ; Sensor Coverage Detection Range: 60 Feet ; Sensor Field Of View: 180 degrees

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923415609
Manufacturers Part Number	65/1413
UPC	045923415609

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING

Packaging

Carton	1
Weight Per each	2.77

Uses, Certifications, and Standards

Application	Outdoor
environmental conditions	Wet
Frequency Rating	50/60
standard	cETLus