ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298



65550 20W Led Vapor Tight Adjustable 3K/4K/5K 2000LM

Satco

Catalog Number	65550
Manufacturer	Satco
Description	Led Adjustable Vapor Tight Fixture - 20W - CCT Selectable 3K/4K/5K - Gray Finish
Weight per unit	5.1 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.167 to 0.072
average life	50000
beam angle	210
Lamp Type	LED
Lamp Wattage	20
lumens	1700 to 2000
Material	Die-Cast Aluminum
Power Source	Hardwired
Temperature Range	to 30 to 2250122
Voltage Rating	120 to 277

Material, Color, and Finish

Finish	Gray
Lens Material	Glass

Dimensions and Weight

Height	13.19
Length	4.72
Width	4.72

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
510 W Jackson Street
38501-0000, TN Cookeville
Phone: 931-271-9933
Fax: 931-545-4298

Descriptions

Description	20W LED VAPOR TIGHT ADJUSTABLE 3K/4K/5K 2000LM
extra long description	SATCO 65/550 LED ADJUSTABLE VAPOR T
Long Description	LED Adjustable Vapor Tight Fixture - 20W - CCT Selectable 3K/4K/5K - Gray Finish
Product Type	Led Adjustable Vapor Tight
Special Features	Warranty: 5-Years ; Location Rating: Wet ; Style: Utility ; JA8 Compliant: False ; Amps: 0.167-0.072A ; Incandescent Equivalent: 125W ; Operating Frequency: 50/60Hz ; Power Factor: >0.9 ; Surge Protection: Built-in surge protection - 2KV ; Wattage Selectable: False ; ADA Compliant: False ; Bulb Included: Integrated ; Beam Angle (degree): 210 ; Cct Selectable: True ; Indoor Outdoor: Outdoor ; IP Rating: IP65 ; Lens Finish: Frost ; Lens Material: Glass ; Mounting Procedure: Ceiling/Wall ; Operating Temp: -30

Manufacturer Information

Brand	Nuvo
GTIN	00045923653087
Manufacturers Part Number	65/550
UPC	045923653087

Taxonomies, Classifications, and Categories

Category Description	LED HAZARDOUS LOCATION & VAPOR TIGHT LIGHTING
Type	Functional Lighting

Packaging

Carton	1
Weight Per each	5.1

Uses, Certifications, and Standards

Application	Outdoor
standard	cETLus - Listed