



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

65718 Led Double Head Security Light 40K BRZ (No Sensor)

Satco



Catalog Number	65718
Manufacturer	Satco
Description	Led Security Light - Dual Head - Bronze Finish - 4000K
Weight per unit	2.5 (lbs/each)
Product Category	Lighting

Features

Lamp Type	LED
Material	Die Cast Aluminum
Number of Lamps	2
Socket Type	Hardwired
surge protection	Built-in surge protection - 2KV
Voltage Rating	277
Warranty	5 Year Limited - Fixtures

Material, Color, and Finish

fixture material	die-cast aluminum
Style	Flood Light

Descriptions

Description	LED DOUBLE HEAD SECURITY LIGHT 40K BRZ (NO SENSOR)
extra long description	SATCO 65/718 LED 2 BULLET HEAD SEC
Long Description	LED Security Light - Dual Head - Bronze Finish - 4000K
Product Type	Led 2 Bullet Head Security LGT BZ 40K
Special Features	Watts: 20W ; Volts: 120V-277V ; Lumens: 1900 ; Color temperature: 4000K Cool White ; CRI: 80 ; Non-Dimmable ; Average rated hours: 50000 ; Warranty: 5 Year Limited - Fixtures ; Beam spread: 50 degrees ; California T24 2016 & 2019 JA8 Compliant - Outdoor LED ; HID equivalent: 70W ; Incandescent equivalent: 125W ; Operating temperature: -30C (-22F) to a maximum of +50C (+122F) ; IP rating: IP65

Manufacturer Information

Brand	Satco
GTIN	00045923629563
Manufacturers Part Number	65/718
UPC	045923629563



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	LED FLOODLIGHTS, WALLPACKS, BOLLARDS & LANDSCAPE LIGHTING
Type	Dual Head

Packaging

Carton	1
Package	5
Weight	2.41
Weight Per each	2.54

Uses, Certifications, and Standards

Application	OUTDOOR LIGHTING
environmental conditions	Outdoor Wet Location
Operating Temperature	-30C (-22F) to a maximum of +50C (+122F)
standard	cETLus