CROUSE-HINDS

Push-in EMT Connectors and Couplings

Crouse-Hinds innovative new Push-in EMT fittings deliver quality, reliability, labor savings, and the lowest installed cost


Applications:

- Used to join EMT conduit to a box or enclosure
- Design prevents water seepage into conduit, box, or enclosure
- For use in drv locations
- For use where raintight fittings are required

Features & Benefits:

- Available in the popular 1/2" and 3/4" trade sizes for both connectors and couplings
- Available in insulated and non-insulated versions to meet customer preference
- Fast installation without the use of any tools
- EMT conduit simply pushes into the fitting
- Concrete tight
- Raintight listed
- Marked raintight on gland nut for easy identification
- Zinc die cast locknut
- Patent pending design
- UL & cUL Listed, File No. E22132

Up to an 85% reduction in labor!



RS Means® is a division of REED Construction Data, LLC and it is a widely accepted publication used for estimating construction cost data.

RS Means budgets that each EMT compression fitting will cost an electrician \$8.21 per fitting with a standard hourly rate of \$72.85 per hour. Our patented EMT Push-In Connector averages a labor cost of under \$1!

Eaton

1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com



Eaton's Crouse-Hinds business 1201 Wolf Street Syracuse, NY 13208 Crouse-Hinds.com

Certifications & Compliances:

- UL and cUL Listed
- UL File No. E-22132

Standard Materials & Finishes:

- Body zinc die cast, natural •
- Gasket polyethylene, natural



Make sure conduit is cut and burs cleaned before installing Push-in EMT fitting into the box and tightening the locknut.

Step



Push-in EMT fitting onto correctly sized ٠ conduit.

Installed!

Straight Connectors – Non-insulated UL File No. E-22132

		(UL)	c (UL)
Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
650RTQ	¹ /2″	50	10.1
651RTQ	³ /4″	25	13.4

Straight Connectors – Insulated UL File No. E-22132

		(UL)	c (U)
Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
1650RTQ	1/2″	50	10.1

25


13.4

16.9

Couplings

1651RTQ 3/4"

UL File No. E-22132



·梁武2王	Т
	C
	C

3/4"

661RTQ

o see how easy Push-in EMT Connectors are to install, use the QR code at left.

25

© 2015 Eaton All Rights Reserved Printed in USA Publication No. 5235-0715 July 2015

Eaton is a registered trademark.

All other trademarks are property of their respective owners