



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 662 1" STL CPLG - Concrete Tight

*Crouse-Hinds*

Catalog Number	662
Manufacturer	Crouse-Hinds
Description	Emt Compression Coupling, 1 In Trade Size, Zinc Plated, 8-1/4 In Length, 0.30 LB
Weight per unit	0.2700 (lbs/each)
Product Category	Steel Compression Emt CPLG

### Features

Material	ZINC PLATED STEEL
----------	-------------------

### Descriptions

Description	1" STL CPLG - CONCRETE TIGHT
-------------	------------------------------

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00784564106629
UPC	784564106629

### Taxonomies, Classifications, and Categories

Category Description	STEEL EMT FITTINGS
Type	COMPRESSION

### Packaging

Carton	25
Weight Per each	0.27

### Uses, Certifications, and Standards

standard	UL, cUL
----------	---------

# Thin Wall Conduit Fittings (for EMT Conduit)

## Compression Type Fittings – Steel

### COMPRESSION TYPE FITTINGS – STEEL

#### Applications:

Thin wall conduit fittings are used:

- To join EMT to a box or enclosure
- To couple two ends of EMT conduit

#### Features:

- Compression type
- Threadless
- Male hub threads – NPSM
- Steel locknuts
- Heavy steel walls
- Standard material: steel
- Standard finish: zinc plated

### Concrete Tight Straight Connectors – Insulated

UL File No. E-22132



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
1650	1/2"	50	11
1651	3/4"	25	16
1652	1"	25	25
1653	1 1/4"	10	43
1654	1 1/2"	10	54
1655	2"	5	76
1656	2 1/2"	2	190
1657	3"	1	300
1658	3 1/2"	1	330
1659	4"	1	360

### Straight Connectors – Non-insulated

UL File No. E-22132



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
650S	1/2"	50	9
651S	3/4"	25	16
652	1"	25	25
653	1 1/4"	10	43
654	1 1/2"	10	54
655	2"	5	76
656	2 1/2"	2	190
657	3"	1	300
658	3 1/2"	1	280
659	4"	1	360

### Couplings

UL File No. E-22132



Cat. #	Size	Unit Qty.	Wt. Lbs. Per 100
660S	1/2"	50	12
661S	3/4"	25	18
662	1"	25	27
663	1 1/4"	10	46
664	1 1/2"	10	63
665	2"	5	92
666	2 1/2"	2	250
667	3"	1	410
668	3 1/2"	1	390
669	4"	1	485

EMT Fittings

### Available in 7 Colors

Crouse-Hinds series painted EMT fittings consists of set screw, compression, insulated and non-insulated EMT fittings. Although red is the most commonly used, other colors offered include white, blue, green, yellow, black, and orange. These can also be used in architectural design, to better match look and feel to suit architectural specification and preference.



Part Number Example:

**650SGreen**

Non-insulated Straight Connector		Color
1/2"	650S	Red
3/4"	651S	White
1"	652	Blue
1 1/4"	653	Yellow
1 1/2"	654	Orange
2"	655	Green
2 1/2"	656	Black
3"	657	
3 1/2"	658	
4"	659	

To order, simply add the name of the color needed after the catalog number.