



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 663WG 3W 15A Tog Switch

*Pass & Seymour/Legrand*

Catalog Number	663WG
Manufacturer	Pass & Seymour/Legrand
Description	Grounding Toggle Switch, 3 Poles, 3 Ways, 15 A, 120 V, Thermoplastic, White, Wall Mount, 1.25 (L) X 1.090 (W) X 3.281 (H) In, 0.15 LB
Weight per unit	0.1490 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	15 A
connection	Grounding
Number of Wires	3 in
Poles	3 in
Wire Size	4 in

### Dimensions and Weight

Size	3.3 in
------	--------

### Descriptions

Description	3W 15A TOG SWITCH
-------------	-------------------

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007663105
sub brand	Pass & Seymour
UPC	785007663105

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Grounding Toggle Switch

### Packaging

Carton	10
Package	100
Weight Per each	0.149

### Uses, Certifications, and Standards

Mounting	WALL
standard	UL 498



## TRADEMASTER GROUNDING TOGGLE SWITCH

663WG | [Pass & Seymour](#)

---

### FEATURES & BENEFITS

Triple Pole Switch in white, with grounded terminals, is made with a thermoplastic toggle and frame. It has a smooth, quiet toggle action and is made with high-impact resistant construction. 15 amps, 120 volts.

\*\*Available in bulk packs of 90. Add "U" to end of Catalog Number. Example: 663WGU

- Thermoplastic toggle and frame.
- Extra-long strap.
- High-impact resistant construction.
- Side wire #12 and #14 AWG.
- Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.
- Smooth, quiet toggle action.
- NAFTA-Compliant Residential Wiring Devices are ideal for use on projects subject to the provisions of the Buy American Act.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond

Product Series: TradeMaster

Type: Toggle

Number Of Poles: 3-way

Special Features: NAFTA Compliant, Self-Grounding

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

cULus: Yes

UL Listing No: FSUL WS896

UL Standard: Yes

UN SPSC: 39121406

#### DIMENSIONS

Depth (US): 1.090"  
Height (US): 3.281"  
Width (US): 1.25"

#### TECHNICAL INFORMATION

Amps: 15A  
Volts: 120VAC  
Volts (AC): 120

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO  
Buy American Act Status: Trade Agreement Act Compliant

