



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



68RCSTBRS Brass Round Recessed Floor Box

Abb Installation Products, Inc

Catalog Number	68RCSTBRS
Manufacturer	Abb Installation Products, Inc
Description	Recessed Service Floor Box Cover Kit, Accepts Duplex Receptacles GFI Receptacles and 2 Port Keystone Data Plate, Black With Brass Flange, For Use With Flush Service Floor Box, 100 Cubic Inches, Opening Diameter 5-5/32 Inches, Base Diameter 6-3/8 Inches, Depth 6 Inches, 3/4 Inch and 1 Inch Conduit Tapping, Plastic, For Power or Communications/Data and Wood Sub-Floor and Raised Floor Applications
Weight per unit	2.1 (lbs/each)
Product Category	Floor Boxes & Accessories

Features

Knockouts	0
Material	Non-Metallic

Material, Color, and Finish

Color	Black with Brass Flange
-------	-------------------------

Descriptions

Description	BRASS ROUND RECESSED FLOOR BOX
extra long description	ABB 68R-CST-BRS RND RECESS CVR, BLK
Long Description	Recessed Service Floor Box Cover Kit, Accepts Duplex Receptacles GFI Receptacles and 2 Port Keystone Data Plate, Black with Brass Flange, For use with Flush Service Floor Box, 100 Cubic Inches, Opening Diameter 5-5/32 Inches, Base Diameter 6-3/8 Inches, Depth 6 Inches, 3/4 Inch and 1 Inch Conduit Tapping, Plastic, For Power or Communications/Data and Wood Sub-Floor and Raised Floor Applications
Product Type	RND Recess CVR, BLK W/ Brass Flange
Special Features	Unique cover provides aesthetic recessed service

Manufacturer Information

Brand	Steel City
GTIN	00785991044447
Manufacturers Part Number	68R-CST-BRS
UPC	785991044447

Taxonomies, Classifications, and Categories

Category Description	FLOOR BOXES
Type	Flush Service



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Packaging

Carton	1
Package	4
Weight Per each	2.07

Uses, Certifications, and Standards

Application	For use with 68 P round floor box
standard	UL E11461 / UL E11461