



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



691W Combo 15A 1 SW 1P-120V 1RECP-125V WH

Pass & Seymour/Legrand

Catalog Number	691W
Manufacturer	Pass & Seymour/Legrand
Description	Combination Switch, 1 Pole, 15 A, 120/125 V, White, 3 Wires, Thermoplastic, 1.32 (L) X 0.94 (W) X 3.28 (H) In, Toggle Actuator, Wall Mount, 0.22 LB
Weight per unit	0.2171 (lbs/each)
Product Category	Combination Devices

Features

actuator	Toggle
amperage rating	15
connection	Side wire
Connection Type	Wired
Contact Rating	15 Amp, 120/125 VAC
indoor/outdoor	Indoor
Load Rating	15 A @ 120/125 VAC
Load Type	Fluorescent, CFL, Halogen, Xenon, Universal, Incandescent, LED
Number of Gangs	1
Number of Switches	1.0
operating cycles	3000
Outlet Type	Indoor
Poles	1
supply voltage	120.0
Switch Type	Toggle
throw type	Single Throw
Voltage	120 VAC, 125 VAC
Wall Plate Included	NO
Wire Size	4

Material, Color, and Finish

Finish	SATIN
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	COMBO 15A 1 SW 1P-120V 1RECP-125V WH
extra long description	P&S 691W COMBO 15A 1 SW 1P-120V 1RE
Special Features	Two devices fits in one space, side wire



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007691023
Manufacturers Part Number	691W
UPC	785007691023

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet, Switch, Combination

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	50
Weight Per each	0.2171

Uses, Certifications, and Standards

environmental conditions	Flammability: UL94 V2
Mounting	WALL
standard	CULUS, UL 498